

Features

- MBNC heavy duty clamp with stainless steel hardware suitable for direct burial
- Can be combined with Universal Pedestal Clamp (UPCJ) for bonding to various pedestal sizes for Mesh Bonding Networks
- Code compliance (NEC[®] Article 250)
- UL[®] 467 Listed

Mesh Bonding Network Connector

MBNC82
MBNC240
MBNC240A



The Mesh Bonding Network Connectors (MBNC) from ERICO allow for fast, simple and economical field connection of grounding and bonding wires. In addition to cross-wire bonding connections, the MBNC can accommodate additional pigtails that can be used to connect to building steel and equipment.

Part Number	Conductor Size Range	Standard Packaging Quantity
MBNC82	#8 AWG - #2 AWG, Solid or Stranded 10 mm ² - 35 mm ²	25
MBNC240	#2 AWG - 4/0 AWG, Solid or Stranded 35 mm ² - 100 mm ²	25
MBNC240A	#2 AWG - 4/0 AWG, Solid or Stranded 35 mm ² - 100 mm ²	25



MBNC82 — Cross Connection



MBNC82 — Parallel Tap



MBNC240A — Cross Connection



MBNC240A — Parallel Tap

NEC is a registered trademark of, and National Electrical Code (NEC) standard is a copyright of the National Fire Protection Association. UL is a registered trademark of UL LLC.

WARNING

ERICO products shall be installed and used only as indicated in ERICO's product instruction sheets and training materials. Instruction sheets are available at www.erico.com and from your ERICO customer service representative. Improper installation, misuse, misapplication or other failure to completely follow ERICO's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death.

Copyright ©2011, 2012 ERICO International Corporation. All rights reserved. CADDY, CADWELD, CRITEC, ERICO, ERIFLEX, ERITECH, and LENTON are registered trademarks of ERICO International Corporation.

