



NVENT CADDY TRUSS-T BAR JOIST HANGER, BOTTOM CHORD














FEATURES

- Easily installs on the bottom chord of engineered open web bar joists from underneath, limiting overhead work
- Innovative attachment effortlessly slides through the middle slot of open web bar joists and quickly locks into place when put under load
- Installation of the complete, self-contained system can be accomplished with one hand and requires no additional special tools
- The unique design of the nVent CADDY Truss-T hanger does not need to be tightened like a traditional beam clamp, providing greater adjustability and speed during system alignment
- Prefabricated single pipe hanger and multi-pipe/tube trapeze assemblies can be prefabricated on the ground or in the shop, and easily hung by the installer
- Concentrically loading the bar joist chord eliminates torsion and/or distortion, adhering to the strict rules established by the Steel Joist Institute (SJI)
- The increased load carrying capacity results in the product being UL listed to support a maximum of 8" Schedule 40 pipe
- · Made in the USA

Material: Steel
Finish: Pregalvanized
Static Load Safaty Fact

Static Load Safety Factor: 3.5:1

Part	Rod Size					Static Load
Number	RS	Α	В	С	D	F
CTH037BC	3/8"	3"	1 1/4"	4 1/2"	1/2" - 1"	1,200 lb
CTH050BC	1/2"	3"	1 1/4"	4 1/2"	1/2" - 1"	1,200 lb



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN RAYCHEM SCHROFF TRACER