



Description: Traditional cable fittings. Known for excellent strain relief even while providing a high protection class. Plastic lock nuts for fixation are included in the delivery.

Material: Fitting body made of polyamide PA6, and sealing made of neoprene.

Temperature resistance: -20°C to +100°C.

Flammability: V-2 according to UL94.

Finish: RAL 7035.

Protection: IP 66

Thread	Cable Size	Pack quantity	CatalogNumber
M12 x 1.5	3 - 6.5	100	CPG12
M16 x 1.5	5 - 10	50	CPG16
M20 x 1.5	6 - 12	50	CPG20
M25 x 1.5	13 - 18	50	CPG25
M32 x 1.5	18 - 25	20	CPG32
M40 x 1.5	22 - 32	10	CPG40
M50 x 1.5	30 - 38	5	CPG50
M63 x 1.5	34 - 44	5	CPG63