



**Description:** Raised roof with 2.5 mm ventilation slots and filter material.

**Material:** 1.5 mm steel plate. Filter material: EU 4 according to DIN 24185.

**Finish:** RAL 7035 structured powder coating.

**Temperature resistance:** 100°C.

**Protection:** Complies with IP 31 | TYPE 1.

**Pack quantity:** 1 piece with mounting brackets and ventilation filter.

**Note:** Increases the enclosure height by 40 mm.

For enclosure		
W	D	Item no.
500	500	CVR0505R5
600	300	CVR0603R5
600	400	CVR0604R5
600	500	CVR0605R5
600	600	CVR0606R5
600	800	CVR0608R5
800	300	CVR0803R5
800	400	CVR0804R5
800	500	CVR0805R5
800	600	CVR0806R5
800	800	CVR0808R5
800	900	CVR0809R5
1000	300	CVR1003R5
1000	400	CVR1004R5
1000	500	CVR1005R5
1000	600	CVR1006R5
1000	800	CVR1008R5
1200	300	CVR1203R5
1200	400	CVR1204R5
1200	500	CVR1205R5
1200	600	CVR1206R5
1200	800	CVR1208R5
1600	400	CVR1604R5
1600	500	CVR1605R5
1600	600	CVR1606R5