

EFA200R5

Exhaust filter

nVent

HOFFMAN

CONNECT AND PROTECT



Cut-out (mm)	125 x 125
Filter mat (EN779)	G4
Filtration efficiency (%)	>90
Weight_ (kg)	0,20
D	26
Item no.	EFA200R5

Description: Exhaust filter to be used for natural ventilation, or for forced ventilation working with filter fans EF. nVent HOFFMAN exhaust filters save us time because are installed with a click-in system without screws. The hinged front cover can be easily opened for quick and easy filter replacement.

Material: Front cover made of injection-moulded thermoplastic, self-extinguishing, UL94V0.

Temperature range: -40 °C to +55 °C.

Protection: IP 54 | TYPE 12.

Finish: RAL 7035.

Approvals: CE, EAC, cRUus_UL Recognized.

Pack quantity: One exhaust filter.

This vertical exhaust filter, EFA, with a IP 54 protection degree, is easy to install thanks to its click-in feature. Unnecessary downtime is avoided, since water and dust are prevented from entering the enclosure through the filter.



IP 54