

EFAE200R5

EMC Exhaust filter



This EMC vertical exhaust filter, EFAE, with a IP 54 protection degree, is easy to install thanks to its click-in feature. Unnecessary downtime is avoided, since water and dust are prevented from entering the enclosure through the filter. EMC performance is maintained on an EMC enclosure with this filter.



IP 54

IP	54
Cut out dim.	126.5 x 126.5
Item no.	EFAE200R5
Filtration efficiency (%)	>90
Filter mat (EN779)	G4
Depth	26

Description: Suitable for specific EMC enclosures. Cutting edge surface of the enclosure needs to be blank for contact.

Material: Plastic, UL94-V0. EMC screen: stainless steel, contact strips.

Approvals: CE, GOST, UR, cUL.

Protection: IP 54.

Pack quantity: 1 filter with housing.