

EFAE220R5

EMC Exhaust filter



IP	54
Cut out dim.	178 x 178
Item no.	EFAE220R5
Filtration efficiency (%)	>90
Filter mat (EN779)	G4
Depth	34

Description: Suitable for specific EMC enclosures. Cutting edge surface of the enclosure needs to be blank for contact.

Material: Plastic, UL94-V0. EMC screen: stainless steel, contact strips.

Approvals: CE, GOST, UR, cUL.

Protection: IP 54.

Pack quantity: 1 filter with housing.

This EMC vertical exhaust filter, EFAE, with a IP 54 protection degree, is easy to install thanks to its click-in feature. Unnecessary downtime is avoided, since water and dust are prevented from entering the enclosure through the filter. EMC performance is maintained on an EMC enclosure with this filter.



IP 54