

CONNECT AND PROTECT



Description: Exhaust filter to be used for natural ventilation, or for forced ventilation working with filter fans EFP. nVent HOFFMAN exhaust filters save us time because are installed with a clickin system without screws. The hinged front cover can be easily opened for quick and easy filter replacement. The new filter mat gives longer life with a low pressure drop because of special construction.

Material: Front cover made of injection-moulded thermoplastic, self-extinguishing, UL94V0. UV resistance.

Temperature range: -40 °C to +55 °C.

Protection: IP 55 | TYPE 12.

Finish: RAL 7035.

Approvals: CE, EAC, cRUus_UL Recognized.

Pack quantity: One exhaust filter.

Filter mat (EN779)	Filtration efficiency (%)	Cut-out (mm)	CatalogNumber
G4	>90	125 × 125	EFAP200R5
G4	>90	177 × 177	EFAP220R5
G4	>90	223 × 223	EFAP250-300R5
G4	>90	291 × 291	EFAP500-700R5