

# EFAP220R5

Exhaust filter, outdoor version

nVent

HOFFMAN

CONNECT AND PROTECT



Cut-out (mm)	177 × 177
Filter mat (EN779)	G4
Filtration efficiency (%)	>90
Item no.	EFAP220R5

**Description:** Exhaust filter to be used for natural ventilation, or for forced ventilation working with filter fans EFP. nVent HOFFMAN exhaust filters save us time because are installed with a clickin system without screws. The hinged front cover can be easily opened for quick and easy filter replacement. The new filter mat gives longer life with a low pressure drop because of special construction.

**Material:** Front cover made of injection-moulded thermoplastic, self-extinguishing, UL94V0. UV resistance.

**Temperature range:** -40 °C to +55 °C.

**Protection:** IP 55 | TYPE 12.

**Finish:** RAL 7035.

**Approvals:** CE, EAC, cRUus\_UL Recognized.

**Pack quantity:** One exhaust filter.

This outdoor vertical exhaust filter, EFAP, with a polycarbonate cover and with a IP 55 protection degree, is easy to install thanks to its click-in feature. Unnecessary downtime is avoided, since water and dust are prevented from entering the enclosure through the filter. This filter is ideal both in indoor and outdoor environments, including direct sunlight thanks to its resistance to UV radiation.

CE UK EAC

IP 55