

EL1200DS

LED Enclosure light with socket



Description: LED enclosure light specially designed for nVent HOFFMAN enclosures. Fast and tool-free assembly thanks to a latching hook system designed to fit the 25mm hole pattern on nVent HOFFMAN enclosures. May be fitted horizontally or vertically.

Lamp type: LED.

Luminosity: 1200 lm.

Light colour: 4000 K (neutral white).

Power consumption: 12 W

Operating voltage: 100 V - 240 V ~, 50/60 Hz

Connection: Infeed, 3-pole. Through wiring, 3-pole.

Operating temperature: -20 °C ... +55 °C

Protection: IP20

Dimensions: 364 × 76 × 48 mm.

Operating voltage	Socket type	Width	Item no.
100 V - 240 V ~, 50/60 Hz	Type F (Shucko)	364	EL1200DS
100 V - 240 V ~, 50/60 Hz	Type E	364	EL1200DS-BF
100 V - 240 V ~, 50/60 Hz	Type J	364	EL1200DS-CH
100 V - 240 V ~, 50/60 Hz	Type G	364	EL1200DS-GB
100 V - 125 V ~, 50/60 Hz	Type B	364	EL1200DS-US