

# HALP163609GE

Aluminium terminal box

nVent

HOFFMAN

CONNECT AND PROTECT



H	160
W	360
D	90
Weight (kg)	2.70
Item no.	HALP163609GE
Body thickness	4.1
Cover thickness	3.7
Thread for mounting plate	M6
Number of cover screws	4

**Material:** Aluminium alloy EN AC-47100.

**Gasket:** Standard supply fitted with a polyurethane gasket. Silicone, neoprene and EPDM gaskets are available on request.

**Temperature resistance:** -30 °C to +80 °C.

**Protection:** IP 66, 67 | IK 09, 08 for HALP050503GE.

**Finish:** RAL 7001.

**Approvals:** CE, GOST. For cULus\_UL Listed approvals, please contact our sales department.

**Delivery:** Body and cover are manufactured from aluminum, cover screws are made of stainless steel.

The aluminium terminal box range, HALP, with a IP 66, 67 protection degree, is available off the shelf in many different sizes. The HALP range is well suited for indoor and outdoor environments thanks to excellent corrosion resistance.

Water and dust are prevented from entering the terminal box, thus eliminating the risk for component failure, and with that, unnecessary downtime.



IP 66, 67 | IK 08/09