



**Description:** DIN rail mounted electrical socket. Pressure clamp connection for easy and quick wiring.

**Dimensions:** 92 mm x 62 mm x 48 mm.

**Connection:** 3 pressure clamps for stranded and rigid wire 0.5-2.5 mm<sup>2</sup>. Integrated fuse 6,3A 5x20 mm.

**Finish:** Light grey.

**Material:** Plastic UL 94 V-0.

**Pack quantity:** 1 piece.

Socket type	Item no.
Schuko	LPS10
France / Belgium / Czech	LPS10FR
Switzerland	LPS10CH
UK / Ireland	LPS10UK
USA / Canada	LPS10USA