

# MPGS12

One-Piece Consoles In Stainless Steel



The stainless steel compact console, MPGS, in a IP66/55 protection degree is available off the shelf. It has a hinged desk panel, and the ergonomic design allows for easy installation and access to HMI-equipment- It also increases the mounting space available. This console can be installed in virtually any environment, grade dependent.



IP 66 | TYPE 4X, 12, 13 | IK 10 (single door); IP 55 | TYPE

## Stainless steel

H	985
W	1200
D	400
h	790
w	1099
d	357.5
Usable depth	357.5
Weight (kg)	90.67
Item no.	MPGS12

**Material:** AISI 304 pre-grained stainless steel / AISI 316L (on request). Body and door: 2 mm. Rear panel: 1.5 mm. Bottom plates: 1.5 mm. Mounting plate: 2.5 mm galvanized steel.

**Body:** Folded and seam welded. Console construction includes a base that provides a distance between the floor and the lower part of the door/s, acting as an integrated plinth.

**Doors and panels:** Single folded surface mounted with hinges, allowing left and right-hand opening to base door. Angle 12° from horizontal. Concealed hinges, on top edge, allow 90° opening. Panel held open by self engage/self release mechanical panel stay. Double door on 1200 wide base units.

**Mounting plate:** Standard mounting plate in base unit.

**Lock:** Double-bit 3 mm locks for top panel. For base, two double-bit 3 mm locks.

**Cable inlet:** Bottom opening for cable access. Bottom plate for cable glanding supplied as standard.

**Earthing:** M8 threaded studs on body, door, top panel and rear panel.

**Finish:** 400 pre-grained stainless steel.

**Protection:** Single door: IP 66 | TYPE 4X, 12, 13 | IK 10. Double door: IP 55 | TYPE 12, 13 | IK 10.

**Delivery:** Mounting plate and suitable nuts and washers for earthing. The console is delivered on a wooden pallet.