

# OABP304013GE

Large ABS terminal box



#### With grey cover

H	300
W	400
D	132
Inner depth (mm)	115
Weight (kg)	2.30
Item no.	OABP304013GE

**Description:** ABS box, halogen-free, suitable for indoor use. Low UV radiation resistance.

**Material:** Body: ABS. Plain cover: ABS. Transparent cover: polycarbonate.

**Gasket:** Polyurethane gasket integrated in the box cover.

**Temperature resistance:** -40 °C to +60 °C.

**Flammability:** UL94 HB.

**Protection:** IP 66, 67 | IK 06 (-25 °C), IK 07 (+35 °C).

**Finish:** RAL 7035.

**Delivery:** Body, cover, cover screws manufactured from polyamide and mounting screws.

This ABS terminal box range, OABP, with a IP 66, 67 protection degree, can be extended in depth. It is available off the shelf in many different sizes. Deeper components may be installed when an extension frame, OPCP-EE, is used. The OABP range is well suited for demanding environments, since water and dust are prevented from entering the terminal box, thus eliminating the risk for component failure, and with that unnecessary downtime.



IP 66,67 | IK 06/07