

# OPCP406013TE

Large polycarbonate terminal box



#### With transparent cover

H	400
W	600
D	132
Inner depth (mm)	115
Weight (kg)	4.50
Item no.	OPCP406013TE

**Description:** Polycarbonate box, halogen-free, suitable for outdoor use. High UV radiation resistance. Self-extinguishing.

**Material:** Polycarbonate.

**Gasket:** Polyurethane gasket integrated in the box cover.

**Temperature resistance:** -40 °C to +80 °C.

**Flammability:** UL746C 5V.

**Protection:** IP 66, 67 | IK 08 (-25 °C ... +35 °C).

**Finish:** RAL 7035.

**Approvals:** CE, GOST. For cULus\_UL Listed, please contact our sales department.

**Delivery:** Body, cover, cover screws manufactured from polyamide and mounting screws.

This polycarbonate terminal box range, OPCP, with a IP 66, 67 protection degree, can be extended in depth. It is available off the shelf in many different sizes. Deeper components may be installed when an extension frame, OPCP-EE, is used. The OPCP range is well suited for indoor and outdoor environments, even in locations where there is direct sunlight, thanks to the resistance to UV radiation. Water and dust are prevented from entering the terminal box, thus eliminating the risk for component failure, and with that, unnecessary downtime.



IP 66, 67 | IK 08