



IP 55 | TYPE 4, 12 | IK 10 - single door; IP 55 | TYPE 12 | IK



The mild steel single door floor standing enclosures sets new standards when it comes to strength and ease of use. From the moment our enclosures arrive in the panel shop, the advantages are plain to see. It's delivered on a pallet of exactly the same size so that it can be combined before the pallet is removed, and the mounting plate is on the outside so you can begin work immediately.

Material: Frame: 1.5 mm painted steel. Door: 2 mm painted steel. Rear, roof and side panels: 1.5 mm painted steel. Mounting plate: 3 mm galvanized steel. Bottom plates: 1 mm galvanized steel.

Frame: Seam welded reversed open profiles with 25 mm hole pattern according to DIN 43660. Including integrated external hole pattern.

Door: Mounted with four hinges allowing left or right hand opening. Including door frame with 25 mm hole pattern.

Rear panel: Fitted by M6 torx screws. Standard facilities for rear door mounting.

Side panels: Supplied as an accessory.

Roof panel: Removable.

Lock: Espagnolette 4-point locking system. Does not interfere with the enclosure inner space. Standard double-bit lock with 3 mm insert. Standard inserts, cylinders, lift handles and T-handles are available as accessories.

Bottom plates: Consists of three or four (D>600) pieces.

Mounting plate: Double folded and adjustable in depth by steps of 25 mm.

Earthing: All panels are earthed through their fittings and are equipped with a separate earthing stud.

Finish: RAL 7035 structured powder coating.

Protection: Complies with IP 55 | TYPE 4, 12 | IK 10 for single door; IP 55 | TYPE 12 | IK 10 for double doors.

Mounting requirements: Standard delivery ready for combined installation. For stand-alone installation add side panels.

Delivery: Frame with fitted door, rear panel, roof panel, bottom plates, mounting plate and door frame. Delivery also includes earthing bolts. Delivered on a pallet which is identical to the width of the enclosure to allow suiting without removal. All packing material is recyclable.

VME

Mild steel combinable version, single door enclosure

H	W	D	h	d	N° of doors	Item no.
1800	600	400	1694	321	1	VME18064CR5
1800	600	500	1694	421	1	VME18065CR5
1800	800	400	1694	321	1	VME18084CR5
1800	800	500	1694	421	1	VME18085CR5
1800	1000	400	1694	321	1	VME18104CR5
1800	1000	500	1694	421	1	VME18105CR5
1800	1200	400	1694	321	2	VME18124CR5
1800	1200	500	1694	421	2	VME18125CR5
1800	1600	400	1694	321	2	VME18164CR5
1800	1600	500	1694	421	2	VME18165CR5
2000	600	400	1894	321	1	VME20064CR5
2000	600	500	1894	421	1	VME20065CR5
2000	600	600	1894	521	1	VME20066CR5
2000	800	400	1894	321	1	VME20084CR5
2000	800	500	1894	421	1	VME20085CR5
2000	1000	400	1894	321	2	VME20104CR5
2000	1000	500	1894	421	2	VME20105CR5
2000	1200	400	1894	321	2	VME20124CR5
2000	1200	500	1894	421	2	VME20125CR5
2000	1200	600	1894	521	2	VME20126CR5
2000	1600	400	1894	321	2	VME20164CR5*

*1600 mm wide mounting plates are supplied as two 800 mm wide mounting plates (MPW2008).

VME

Mild steel combinable version, single door enclosure