

SPM-IEC_NA

Side panels | Floor Standing Enclosures



HOFFMAN

CONNECT AND PROTECT



Description: Easy one man assembly. Sealed by an extruded, one piece polyurethane gasket and mounted with 8 screws. Can be replaced by the side door DNS.

Material: 1.5 mm steel plate.

Finish: RAL 7035 structured powder coating.

Protection: IP 55 | TYPE 12 in combination with MCS.
IP66 | TYPE 4, 12 in combination with MCS-HP.

Pack quantity: 2 panels with mounting accessories.

For enclosure		
H	D	Item no.
1100	600	SPM1106R5
1400	600	SPM1406R5
1400	500	SPM1405R5
1600	500	SPM1605R5
1600	600	SPM1606R5
1800	400	SPM1804R5
1800	500	SPM1805R5
1800	600	SPM1806R5
1800	800	SPM1808R5
2000	400	SPM2004R5
2000	500	SPM2005R5
2000	600	SPM2006R5
2000	800	SPM2008R5
2200	500	SPM2205R5
2200	600	SPM2206R5
2200	800	SPM2208R5



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN RAYCHEM SCHROFF TRACER