



NVENT CADDY SPEED LINK SLS WITH WEDGE ANCHOR



CERTIFICATIONS



FEATURES

Complete system includes wire, locking device and wedge anchor from Powers Fasteners, Inc.

Quickly and easily attaches into cracked and non-cracked concrete

Installs in strut profiles without the need to insert fingers or tools into the strut

Finger tightening of nut secures the locking device into position without tools

No special tools required

ETA-13/0355 assessment available for wedge anchor from Powers Fasteners, Inc-

SPECIFICATIONS

- Wire Rope Diameter:** 2 mm
- Static Load Safety Factor:** 5:1
- Finish:** Electrogalvanized
- Material:** Steel; Polypropylene; Zinc Alloy
- Complies With:** SMACNA HVAC-DCS

Catalog Number	Item Name	Wire Rope Length	Length(L)	Drill Bit Diameter	Drill Hole Depth	Embedment Depth	Static Load(F)
SLS2L3WA6	196759	3 m	63.500 mm	6 mm	60 mm	55 mm Min	270 N

Catalog Number	Item Name	Wire Rope Length	Length(L)	Drill Bit Diameter	Drill Hole Depth	Embedment Depth	Static Load(F)
SLS2L5WA6	196760	5 m	63.500 mm	6 mm	60 mm	55 mm Min	270 N


- Slot Size(SS):** 8 x 6.5 mm - 8 x 10 mm
Hole Size(HS): 8 – 10 mm
Width(W): 16 mm
Height 2(H2): 43.5 mm
Height 1(H1): 53 mm
Thread Size(TS): M8
Thickness(T): 4 mm Max

ADDITIONAL PRODUCT DETAILS

The 2 mm locking device is compatible with C-Channel Types E0 and E0L.

Total load per wire on a multi-tier trapeze must not exceed static load.

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER