


FC NVENT ERIFLEX FLEXIBAR TO BUSBAR CLAMP



CERTIFICATIONS



FEATURES

Connects nVent ERIFLEX Flexibar to copper busbar

Two plates complete with screws

Allows for excellent electrical contact

Installs quickly and easily

Ideal for on site modifications

RoHS compliant


SPECIFICATIONS

- Quality Class:** 8.8
- Clamping Capacity:** 20 mm
- Finish:** Electrogalvanized
- Material:** Steel

Catalog Number	Item Name	Busbar Width	Conductor Width	Width(W)	Height(H)	A	B	Screw Diameter (Sc)	Torque(TQ)	Unit Weight
FC50X24	553020	50 mm	20 – 24 mm	52 mm	75 mm	36 mm	60 mm	M8	10 N-m	0.319 kg
FC50X32	553030	50 mm	32 mm	60 mm	75 mm	44 mm	60 mm	M8	10 N-m	0.362 kg

Catalog Number	Item Name	Busbar Width	Conductor Width	Width(W)	Height(H)	A	B	Screw Diameter (Sc)	Torque(TQ)	Unit Weight
FC50X40	553040	50 mm	40 mm	68 mm	75 mm	52 mm	60 mm	M8	10 N-m	0.412 kg
FC80X24	553050	80 mm	20 – 24 mm	52 mm	105 mm	36 mm	90 mm	M8	10 N-m	0.432 kg
FC80X32	553060	80 mm	32 mm	60 mm	105 mm	44 mm	90 mm	M8	10 N-m	0.492 kg
FC80X50	553070	80 mm	50 mm	78 mm	105 mm	62 mm	90 mm	M8	10 N-m	0.642 kg
FC100X32	568700	100 mm	32 mm	60 mm	125 mm	44 mm	110 mm	M8	10 N-m	0.670 kg
FC120X32	568730	120 mm	32 mm	60 mm	145 mm	44 mm	130 mm	M8	10 N-m	0.760 kg

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:
nVent.com **CADDY ERICO HOFFMAN RAYCHEM SCHROFF**
TRACER