


DROP-IN LOOP HANGER



FEATURES

- Next generation loop hanger revolutionizes the installation of pipe
- Once on the guide arm, the weight of the pipe opens the self-closing latch and effortlessly guides the pipe into place
- Integrated rubber sleeve is designed to provide additional grip when adjusting hanger height and reduce hanger rotation around the barrel nut
- Eliminates the need to disassemble the hanger during installation
- Allows prefabrication of complex assemblies with fittings, sprinkler heads, and branch lines that previously could not be installed in one piece
- Designed to reduce overhead work for a safer, less strenuous installation

Material: Steel
Finish: Electrogalvanized



Part Number	Article Number	Pipe Size	NB/ DN	Outer Diameter OD	Rod Size RS	A	B	C	D	Installation Height H	Static Load F
DHM0100EG	598984	1"	25	33.7 mm	M10	111.1 mm	65.1 mm	55.6 mm	75.5 mm	88.9 mm Min	1,334 N
DHM0125EG	598985	1 1/4"	32	42.4 mm	M10	127.0 mm	79.4 mm	63.5 mm	90.7 mm	104.8 mm Min	1,334 N
DHM0150EG	598994	1 1/2"	40	48.3 mm	M10	139.7 mm	87.3 mm	69.9 mm	100.4 mm	111.1 mm Min	1,334 N
DHM0200EG	598995	2"	50	60.3 mm	M10	163.5 mm	104.8 mm	82.6 mm	125.0 mm	133.4 mm Min	1,334 N

Installation Height represents the clearance distance needed from the loop hanger guide arm to structure to allow for installation of pipe.

DH SURGE RESTRAINT



Material: Steel
Finish: Electrogalvanized



Part Number	Article Number	Pipe Size	Height H
SR0100EG	597866	1"	70.4 mm
SR0125EG	597867	1 1/4"	78.2 mm
SR0150EG	597868	1 1/2"	83.8 mm
SR0200EG	597869	2"	97.8 mm



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN RAYCHEM SCHROFF TRACER

WARNING

nVent products shall be installed and used only as indicated in nVent product instruction sheets and training materials. Instruction sheets are available at nVent.com/ERICO and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

©2018 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners.

nVent reserves the right to change specifications without notice

CADDY-DS-B1250S-B327LT16EUN-EN-1805