



SNAP CLOSE CONDUIT/PIPE CLAMP



CERTIFICATIONS



FEATURES

May be used for either vertical or horizontal installations

Eliminates need for offset bending conduit

Finger closure, no tools required

SPECIFICATIONS


Finish nVent CADDY Armour

Material Spring Steel

Catalog Number	Flexible Conduit Size	MC/AC Cable Size	EMT Conduit Size	Rigid Conduit/Pipe Size	Outer Diameter(OD)	Hole Size(HS)	Hole Type	Static Load 1(F1)	Static Load 2(F2)
16M4I			3/4", 1"	3/4", 1"	0.922" – 1.378"	1/4"	Threaded	100 lb	25 lb
20M4I			1 1/4"	1 1/4"	1.378" – 1.654"	1/4"	Threaded	100 lb	25 lb
24M4I			1 1/2"	1 1/2"	1.654" – 1.969"	1/4"	Threaded	100 lb	25 lb
32M4I			2"	2"	1.969" – 2.362"	1/4"	Threaded	100 lb	25 lb
6M4I	3/8"	14-2 to 12-3			0.551" – 0.709"	1/4"	Threaded	100 lb	25 lb

Catalog Number	Flexible Conduit Size	MC/AC Cable Size	EMT Conduit Size	Rigid Conduit/Pipe Size	Outer Diameter(OD)	Hole Size(HS)	Hole Type	Static Load 1(F1)	Static Load 2(F2)
812M4I			1/2", 3/4"	1/2", 3/4"	0.709" – 1.181"	1/4"	Threaded	100 lb	25 lb
16M			3/4", 1"	3/4", 1"	0.922" – 1.378"	9/32"	Plain	100 lb	25 lb
20M			1 1/4"	1 1/4"	1.378" – 1.654"	9/32"	Plain	100 lb	25 lb
24M			1 1/2"	1 1/2"	1.654" – 1.969"	9/32"	Plain	100 lb	25 lb
32M			2"	2"	1.969" – 2.362"	9/32"	Plain	100 lb	25 lb
6M	3/8"	14-2 to 12-3			0.551" – 0.709"	9/32"	Plain	100 lb	25 lb
812M			1/2", 3/4"	1/2", 3/4"	0.709" – 1.181"	9/32"	Plain	100 lb	25 lb

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF TRACER

© 2022 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners.

nVent reserves the right to change specifications without notice.