




# NVENT CADDY BOX MOUNTING PLATE WITH FAR SIDE SUPPORT ON STUD ASSEMBLY



## FEATURES

Integral far side support for installation on any stud depth

Extruded holes allow mounting of mud rings for both power and data applications

Snaps onto Heavy Duty Telescoping Box Bracket (TB1624HD) bracket for between stud applications

## SPECIFICATIONS

**Finish** Pregalvanized

**Material** Steel

Catalog Number	Knockout Sizes	Box Depth	Box Size	Box Volume	Drywall Thickness	Gang	Ground Wire Included	Mud Ring Type
PK4DV2	(4) 1/2", 3/4", (8) 1/2"	2 1/8"	4"	30.3 in <sup>3</sup>	5/8" - 1 1/2"	2	Yes	Adjustable
PK4DM1	(4) 1/2", 3/4", (8) 1/2"	2 1/8"	4"	30.3 in <sup>3</sup>	3/4"	1	Yes	Raised
PK4DM2	(4) 1/2", 3/4", (8) 1/2"	2 1/8"	4"	30.3 in <sup>3</sup>	3/4"	2	Yes	Raised
PKD1M5	(4) 1", (4) 1- 1/4"	2 1/8"	4 11/16"	42 in <sup>3</sup>	3/4"	1	No	Raised
PKP1M5	(12) 1/2", 3/4"	2 1/8"	4 11/16"	42 in <sup>3</sup>	3/4"	1	Yes	Raised
PKP1M6	(12) 1/2", 3/4"	2 1/8"	4 11/16"	42 in <sup>3</sup>	3/4"	2	Yes	Raised
PK4DV1	(4) 1/2", 3/4", (8) 1/2"	2 1/8"	4"	30.3 in <sup>3</sup>	3/4" - 1 1/2"	1	Yes	Adjustable
PK4D	(4) 1/2", 3/4", (8) 1/2"	2 1/8"	4"	30.3 in <sup>3</sup>			Yes	
PKD1	(4) 1", (4) 1- 1/4"	2 1/8"	4 11/16"	42 in <sup>3</sup>			No	

Catalog Number	Knockout Sizes	Box Depth	Box Size	Box Volume	Drywall Thickness	Gang	Ground Wire Included	Mud Ring Type
PKP1	(12) 1/2", 3/4"	2 1/8"	4 11/16"	42 in <sup>3</sup>			Yes	

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical Support

### Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

### Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

### APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

**nVent.com** CADDY ERICO HOFFMAN RAYCHEM SCHROFF TRACER

© 2022 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners.

nVent reserves the right to change specifications without notice.