




## USC UNIVERSAL STRUT CLAMP FOR COPPER TUBE



### FEATURES

Consists of two clamps, nut and bolt

Fits into open side of strut channel

FM® Specification Tested (from 1/2" to 4" of Copper Tube Size)

### SPECIFICATIONS


**Finish** Polyester

**Material** Steel

Catalog Number	Outer Diameter(OD)	Copper Tube Size	Width(W)	Thickness(T)	Static Load(F)
USC010BR	0.380"	1/4"	1 1/4"	16 GA	450 lb
USC013BR	0.500" – 0.540"	3/8"	1 1/4"	16 GA	450 lb
USC016BR	0.580" – 0.630"	1/2"	1 1/4"	16 GA	450 lb
USC020BR	0.710" – 0.790"	5/8"	1 1/4"	16 GA	450 lb
USC022BR	0.850" – 0.880"	3/4"	1 1/4"	16 GA	450 lb
USC028BR	1.100" – 1.140"	1"	1 1/4"	16 GA	450 lb
USC036BR	1.330" – 1.500"	1 1/4"	1 1/4"	14 GA	600 lb
USC040BR	1.510" – 1.600"		1 1/4"	14 GA	600 lb
USC042BR	1.630" – 1.670"	1 1/2"	1 1/4"	14 GA	600 lb
USC053BR	1.980" – 2.110"		1 1/4"	12 GA	850 lb
USC054BR	2.120" – 2.170"	2"	1 1/4"	12 GA	850 lb
USC068BR	2.600" – 2.720"	2 1/2"	1 1/4"	12 GA	850 lb
USC080BR	3.040" – 3.250"	3"	1 1/4"	12 GA	850 lb
USC107BR	4.100" – 4.330"	4"	1 1/4"	12 GA	850 lb
USC129BR	5.000" – 5.130"	5"	1 1/4"	12 GA	850 lb

Catalog Number	Outer Diameter(OD)	Copper Tube Size	Width(W)	Thickness(T)	Static Load(F)
USC159BR	6.130" – 6.380"	6"	1 1/4"	11 GA	900 lb

## DIAGRAMS



## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical Support

### Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

### Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

### APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

**nVent.com** CADDY ERICO HOFFMAN RAYCHEM SCHROFF TRACER

© 2022 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners.

nVent reserves the right to change specifications without notice.