

THROUGH ROOF PVC ASSEMBLY, PARALLEL CONDUCTOR TO IN-LINE CONDUCTOR



CERTIFICATIONS



FEATURES

Allows for lightning protection conductors to be concealed in ceiling or walls

Use in-line connection for conductor and secure to structure using base plate

SPECIFICATIONS


Conductor Size, UL Class 1 - Class 2 (4/0 Max)

| Catalog Number | Material | Connection Material, In-Line Conductor | Connection Material, Parallel Conductor | Rod Length(L) | Rod Size(R S) | Outer Diameter(O D) | Unit Weight |
|----------------|-----------------------------------------------------------------------|----------------------------------------|-----------------------------------------|---------------|---------------|---------------------|-------------|
| LPC66518 | Copper, Polyvinylchloride, Stainless Steel 18-8 (EN 1.4305) | Copper | Copper | 20" | 1/2" | 1.900" | 2.785 lb |
| LPC66518BI | Aluminum, Copper, Polyvinylchloride, Stainless Steel 18-8 (EN 1.4305) | Copper | Bi-Metallic | 20" | 1/2" | 1.900" | 2.745 lb |
| LPC66524 | Copper, Polyvinylchloride, Stainless Steel 18-8 (EN 1.4305) | Copper | Copper | 26" | 1/2" | 1.900" | 3.195 lb |
| LPC66524BI | Aluminum, Copper, Polyvinylchloride, Stainless Steel 18-8 (EN 1.4305) | Copper | Bi-Metallic | 26" | 1/2" | 1.900" | 3.190 lb |

ADDITIONAL PRODUCT DETAILS

Always consult the roof manufacturer or owner for proper flashing materials.

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF TRACER

© 2022 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners.

nVent reserves the right to change specifications without notice.