TBP1LV, TBP2LV, TBP3LV, TBP4LV
Low Voltage Center Plate for TB1624HD

Part Number	Description
TBP1LV	Single Gang Low Voltage Center Plate
TBP2LV	Double Gang Low Voltage Center Plate
TBP3LV	Three Gang Low Voltage Center Plate
TBP4LV	Four Gang Low Voltage Center Plate

As Shipped



TBP1LV TBP2LV TBP3LV TBP4LV

Install MPCB1220 1st means of support on TBP1LV/TBP2LV/TBP3LV/TBP4LV (Optional)



see Page 2

WARNING:
1. nVent products shall be installed and used only as indicated in nVent product instruction sheets and training materials. Instruction sheets are available at www.nVent.com and from your nVent customer service representative.
2. nVent products must never be used for a purpose other than the purpose for which they were designed or in a manner that exceeds specified load ratings.
3. All instructions must be completely followed to ensure proper and safe installation and performance.
4. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and/or death, and void your warranty.
5. Products that are manufactured using spring steel components shall be used only in a non-corrosive indoor environment.
6. All pipe supports, hangers, intermediate components and structural attachments must ONLY be used as described herein and are NEVER to be used for any other purpose.

NOTE: All load ratings are for static conditions and do not account for dynamic loading such as wind, water or seismic loads, unless otherwise noted.

The customer is responsible for:
a. Conformance to all governing codes.
b. The integrity of structures to which the products are attached, including their capability of safely accepting the loads imposed, as evaluated by a qualified engineer.
c. Using appropriate industry standard hardware as noted above.

SAFETY INSTRUCTIONS:
All governing codes and regulations and those required by the job site must be observed.
Always use appropriate safety equipment such as eye protection, hard hat, and gloves as appropriate to the application.

nVent, nVent CADDY, nVent ERICO Cadweld, nVent ERICO Critec, nVent ERICO, nVent ERIFLEX, and nVent LENTON are owned by nVent or its global affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without prior notice.

© 2021 nVent All Rights Reserved

Assembly on TB1624HD

1 Snap TBPxLV onto TB1624HD



2 Bend two tabs 90˚ (optional) - do not overbend tab to allow sliding



3 Slide center plate to desired position and secure center plate with (2) screws



Mounting on Stud



nVent, nVent CADDY, nVent ERICO Cadweld, nVent ERICO Critec, nVent ERICO, nVent ERIFLEX, and nVent LENTON are owned by nVent or its global affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without prior notice.

© 2021 nVent All Rights Reserved