


# CPNAM Series Decking Offset Clips and Box / Conduit Hangers



**WARNING:**

1. ERICO products shall be installed and used only as indicated in ERICO product instruction sheets and training materials. Instruction sheets are available at [www.erico.com](http://www.erico.com) and from your ERICO customer service representative.
2. ERICO products must never be used for a purpose other than the purpose for which they were designed or in a manner that exceeds specified load ratings.
3. All instructions must be completely followed to ensure proper and safe installation and performance.
4. Improper installation, misuse, misapplication or other failure to completely follow ERICO's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death.
5. Products that are manufactured using spring steel components shall be used only in a non-corrosive indoor environment.
6. All pipe supports, hangers, intermediate components and structural attachments must ONLY be used as described herein and are NEVER to be used for any other purpose.

NOTE: All load ratings are for static conditions and do not account for dynamic loading such as wind, water or seismic loads, unless otherwise noted.

The customer is responsible for:

- a. Conformance to all governing codes.
- b. The integrity of structures to which the products are attached, including their capability of safely accepting the loads imposed, as evaluated by a qualified engineer.
- c. Using appropriate industry standard hardware as noted above.

**SAFETY INSTRUCTIONS:**

All governing codes and regulations and those required by the job site must be observed.  
Always use appropriate safety equipment such as eye protection, hard hat, and gloves as appropriate to the application.



CADDY, CADWELD, CRITEC, ERICO, ERIFLEX, ERITECH, and LENTON are registered trademarks of ERICO International Corporation.

TECHNICAL SUPPORT:

[www.erico.com](http://www.erico.com)


CFS434\_C

1 OF 4


© 2010, 2015 ERICO International Corporation



# CPNAM Series Decking Offset Clips and Box / Conduit Hangers



Part Number  
CPNAM




Static Load Limit 100 lbs (450 N)  
Note: Static load limits apply to  
CADDY® fasteners only




# CPNAM Series Decking Offset Clips and Box / Conduit Hangers


Part Number  
6MCPNAM  
812MCPNAM  
16MCPNAM  
20MCPNAM  
24MCPNAM



↓  
Static Load Limit 100 lbs (450 N)  
Note: Static load limits apply to  
CADDY® fasteners only




Step 1




Step 2


Part Number  
CD0BCPNAM  
CD1BCPNAM  
CD2BCPNAM  
CD2.5BCPNAM




↓  
Static Load Limit 100 lbs (450 N)  
Note: Static load limits apply to  
CADDY® fasteners only



Step 1



Step 2




Step 3




# CPNAM Series Decking Offset Clips and Box / Conduit Hangers

Part Number  
B18SBT18CPNAM



Static Load Limit 50 lbs (225 N)  
(Includes conduit and box)  
Note: Static load limits apply to  
CADDY® fasteners only




Step 1


Step 2

\*See additional assembly instructions  
below in steps 1 - 3


Part Number  
6MB18CPNAM  
812MB18CPNAM  
16MB18CPNAM




Static Load Limit 50 lbs (225 N)  
(Includes conduit and box)  
Note: Static load limits apply to  
CADDY® fasteners only



Step 1 - Attach box with self tapping screws (SMS8).



Step 2 - Install conduit in box.



Step 3 - Finger snap clips closed around conduit.

