


# nVent CADDY Small Packs









## SMALL PACKS FOR RETAIL SALES













### FEATURES

- Small packs in resealable foil bags
- Documentation in each bag
- Additional selection in small packs available on [nVent.com/CADDY](http://nVent.com/CADDY)

- User manual and warning notes available on [nVent.com/CADDY](http://nVent.com/CADDY)



	Part Number	Article Number	Blister VPE	Flange Thickness mm	Conduit OD mm	Standard Global Part Number	Standard Article Number	VPE	Comment		
<b>SC Cable Snap Clip - Spring Steel</b>											
	24SC1011R25	191001	1 box = 4 bags of 25 pcs each	2 - 4	10 - 11	24SC1011	187550	100			
	24SC1214R25	191002		2 - 4	12 - 14	24SC1214	187570	100			
	24SC1518R25	191003		2 - 4	15 - 18	24SC1518	187590	100			
	24SC1924R25	191004		2 - 4	19 - 24	24SC1924	187610	100			
	24SC2530R25	191005		2 - 4	25 - 30	24SC2530	187630	100			
	47SC1011R25	191007		4 - 7	10 - 11	47SC1011	187540	100			
	47SC1214R25	191008		4 - 7	12 - 14	47SC1214	187560	100			
	47SC1518R25	191009		4 - 7	15 - 18	47SC1518	187580	100			
	47SC1924R25	191010		4 - 7	19 - 24	47SC1924	187600	100			
	47SC2530R25	191011		4 - 7	25 - 30	47SC2530	187620	100			
	812SC1011R25	191013		8 - 12	10 - 11	812SC1011	187660	100			
	812SC1214R25	191014		8 - 12	12 - 14	812SC1214	187670	100			
	812SC1518R25	191015		8 - 12	15 - 18	812SC1518	187680	100			
	812SC1924R25	191016		8 - 12	19 - 24	812SC1924	187690	100			
	812SC2530R25	191017		8 - 12	25 - 30	812SC2530	187700	100			
	<b>Cable Tie Holder with Flange Clip - Spring Steel</b>										
		4H24CTR5		191021	1 box = 10 bags of 5 pcs each	3 - 8	N/A	4H24CT	178520	100	
4H58CTR5		191022	8 - 14	N/A		4H58CT	178530	100			
4H912CTR5		191023	14 - 20	N/A		4H912CT	178540	100			
<b>Hammer-On Flange Clip, Side Mount - Spring Steel</b>											
	4H24R5	191018	1 box = 10 bags of 5 pcs each	3 - 8	N/A	4H24	170020	100	CE UL		
	4H58R5	191019		8 - 14	N/A	4H58	170030	100			
	4H912R5	191045		14 - 20	N/A	4H912	170040	100			
<b>Hammer-On Flange Clip, Bottom Mount - Spring Steel</b>											
	EM24R5	191026	1 box = 8 bags of 5 pcs each	3 - 8	N/A	EM24	170050	100	CE		
	EM58R5	191027		8 - 14	N/A	EM58	170060	100			
	EM912R5	191028		14 - 20	N/A	EM912	170070	100			
<b>Hammer-On Flange Clip, Bottom Mount with Stud - Spring Steel</b>											
	EM58SM16R5	191044	1 box = 8 bags of 5 pcs each	8 - 14	N/A	EM58SM16	160450	100			
<b>J-TI/T Rod to C Purlin Clip - Spring Steel</b>											
	J1M10TIR5	191042	1 box = 10 bags of 5 pcs each	1.5 - 4.0	N/A	J1M10TI	175050	100			

	Part Number	Article Number	Blister VPE	Flange Thickness mm	Conduit OD mm	Standard Global Part Number	Standard Article Number	VPE	Comment
<b>Cable/Conduit Clip – Spring Steel</b>									
	K12R10	191032	1 box = 10 bags of 10 pcs each		24 max	K12	170670	100	
	K16R5	191038			30 max	K16	170680	100	
<b>Wire Basket Tray Clip – Spring Steel</b>									
	KBTR5	191043	1 box = 10 bags of 5 pcs each	N/A	N/A	KBT	170011	100	
<b>H-Ti/T Rod to Flange Clip – Spring Steel</b>									
	M6TI24R5	191024	1 box = 10 bags of 5 pcs each	3 - 8	N/A	M6TI24	174820	100	
	M6TI58R5	191025		8 - 14	N/A	M6TI58	174830	100	
<b>Speed Link SLK with Loop end-fitting</b>									
	SLK15L1LPR2	196628	1 box = 15 bags of 2 pcs each	N/A	N/A	SLK15L1LP	196601	20	
	SLK15L2LPR2	196629		N/A	N/A	SLK15L2LP	196514	20	
	SLK15L3LPR2	196630		N/A	N/A	SLK15L3LP	196515	20	
	SLK15L5LPR2	196631		N/A	N/A	SLK15L5LP	196516	20	
<b>Speed Link SLK with Hook end-fitting</b>									
	SLK15L2R2	196614	1 box = 15 bags of 2 pcs each	N/A	N/A	SLK15L2	196509	20	
	SLK15L3R2	196615		N/A	N/A	SLK15L3	196510	20	
	SLK15L5R2	196616		N/A	N/A	SLK15L5	196511	20	
	SLK2L2R2	196619		N/A	N/A	SLK2L2	196538	10	
	SLK2L3R2	196620		N/A	N/A	SLK2L3	196539	10	
	SLK2L5R2	196621		N/A	N/A	SLK2L5	196540	10	
	SLK2L10R2	196622		N/A	N/A	SLK2L10	196542	5	
	SLK3L3R2	196625		N/A	N/A	SLK3L3	196702	10	
SLK3L5R2	196626	N/A	N/A	SLK3L5	196703	5x10 pc			
<b>Speed Link SLK with Toggle end-fitting</b>									
	SLK15L2TR2	196644	1 box = 15 bags of 2 pcs each	N/A	N/A	SLK15L2T	196522	20	
	SLK15L3TR2	196645		N/A	N/A	SLK15L3T	196523	20	
<b>Speed Link SLK with Y-Toggle end-fitting</b>									
	SLK15Y300L3R2	196648	1 box = 15 bags of 2 pcs each	N/A	N/A	N/A	N/A	N/A	

\*Please note the load values shown in our documentation!



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN RAYCHEM SCHROFF TRACER**