



nVent CADDY Heavy Duty Telescoping Bracket Between Stud Assembly



CONNECT AND PROTECT

The nVent CADDY Heavy Duty Telescoping Bracket Between Stud Assembly line increases overall productivity, savings, and job site safety. For ultimate flexibility, the assemblies are configured with the most common box and mud ring combinations. The line is also offered in both standard and open back boxes as well as in single and double gang fixed or adjustable depth mud rings. When paired with the nVent CADDY Open Back Box, the assembly is ideal for prefab installations where devices, fittings, and cables are installed to quickly and easily complete make-up wiring connections, without the need to drop or work through the mud ring.



FEATURES

- Rigid and versatile - add/remove boxes quickly and easily
- Prefab tab to prevent disassembly during transport, but allows for sliding on main bracket prior to final securement
- Bracket will telescope and allow for easy positioning within wall stud
- Box center plates slide to desired position prior to final securement

Finish: Pregalvanized
Material: Steel

| Catalog Number | Stud Spacing | Knockout Sizes, Box 1 | Knockout Sizes, Box 2 | Box Type | Gang, Box 1 | Gang, Box 2 | Mud Ring Type | Box Depth | Box Size 1 | Box Size 2 | Ground Wire Included | Volume, Box 1 | Volume, Box 2 | Drywall Thickness |
|----------------|--------------|-----------------------|-----------------------|----------|-------------|-------------|---------------|-----------|------------|------------|----------------------|---------------|---------------|-------------------|
| TBP4D | 14½" – 25" | (4) ½", ¾", (8) ½" | – | Closed | – | – | – | 2⅞" | 4" | – | Yes | 30.3 in³ | – | – |
| TBP4DV1 | 14½" – 25" | (4) ½", ¾", (8) ½" | – | Closed | 1 | – | Adjustable | 2⅞" | 4" | – | Yes | 30.3 in³ | – | ⅝" – 1½" |
| TBP4DM1 | 14½" – 25" | (4) ½", ¾", (8) ½" | – | Closed | 1 | – | Raised | 2⅞" | 4" | – | Yes | 30.3 in³ | – | ⅝" |
| TBP4DPD1 | 14½" – 25" | (4) ½", ¾", (8) ½" | (4) 1", (4) 1¼" | Closed | – | – | – | 2⅞" | 4" | 4⅜" | Yes | 30.3 in³ | 42 in³ | – |
| TBP4DM1PP1M5 | 14½" – 25" | (4) ½", ¾", (8) ½" | (12) ½", ¾" | – | 1 | 1 | Raised | 2⅞" | 4" | 4⅜" | Yes | 30.3 in³ | 42 in³ | ⅝" |
| TBP4DPP1 | 14½" – 25" | (4) ½", ¾", (8) ½" | (12) ½", ¾" | Closed | – | – | – | 2⅞" | 4" | 4⅜" | Yes | 30.3 in³ | 42 in³ | – |
| TBPX4 | 14½" – 25" | (4) ½", ¾", (7) ½" | – | Open | – | – | – | 2⅞" | 4" | – | Yes | 32.8 in³ | – | – |
| TBPX4V1 | 14½" – 25" | (4) ½", ¾", (7) ½" | – | Open | 1 | – | Adjustable | 2⅞" | 4" | – | Yes | 32.8 in³ | – | ⅝" – 1½" |
| TBPX4M1 | 14½" – 25" | (4) ½", ¾", (7) ½" | – | Open | 1 | – | Raised | 2⅞" | 4" | – | Yes | 32.8 in³ | – | ⅝" |



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN RAYCHEM SCHROFF TRACER