

Ultimate Position Splice Kit MT12 and FT12



CONNECT AND PROTECT



MT12 MALE TAPER STUD



Material: Steel | Finish: Plain

FEATURES

- Slim design maintains concrete cover
- Installs quickly and easily
- Utilizes the standard nVent LENTON taper profile
- No special tools or skills required
- Designed to splice the same diameter bars where the second bar can be rotated and is not restricted in its axial direction

FT12 FEMALE STANDARD COUPLER



Material: Steel | Finish: Plain



Part Number	Hex Width W	Diameter Ø	Length L	Bar Depth BD	Unit Weight
LU12MT12D	0.69"	—	1.66"	0.84"	0.1 lb
LU16MT12D	0.88"	—	1.89"	1.06"	0.2 lb
LU20MT12D	1.06"	—	2.41"	1.54"	0.4 lb
LU22MT12D	1.06"	—	2.66"	1.63"	0.5 lb
LU25MT12D	1.19"	—	2.80"	1.73"	0.6 lb
LU28MT12D	—	1.38"	2.88"	1.82"	0.8 lb
LU32MT12D	—	1.50"	3.21"	1.95"	1.2 lb
LU36MT12D	—	1.75"	3.47"	2.21"	1.6 lb
LU43TMT12D	—	2.00"	4.48"	2.90"	2.8 lb
LU57TMT12D	—	2.50"	5.40"	3.57"	5.8 lb

Rebar Size, US
#4
#5
#6
#7
#8
#9
#10
#11
#14
#18

Part Number	Hex Width W	Diameter Ø	Length L	Bar Depth BD	Unit Weight
LU12FT12D	0.69"	—	1.54"	0.84"	0.1 lb
LU16FT12D	0.88"	—	1.82"	1.06"	0.2 lb
LU20FT12D	1.06"	—	2.48"	1.54"	0.5 lb
LU22FT12D	1.19"	—	2.60"	1.63"	0.6 lb
LU25FT12D	—	1.38"	2.77"	1.73"	0.8 lb
LU28FT12D	—	1.50"	2.87"	1.82"	0.9 lb
LU32FT12D	—	1.75"	3.04"	1.95"	1.3 lb
LU36FT12D	—	1.88"	3.37"	2.21"	1.6 lb
LU43TFT12D	—	2.25"	4.39"	2.90"	3.0 lb
LU57TFT12D	—	3.00"	5.23"	3.57"	6.4 lb

Bar dimensions and weights listed may vary by region. Coupler sizes not shown may be available by special order. Contact your nVent LENTON representative for more information.

Designed to Meet: AASHTO, ABNT NBR 8548:1984, ACI 318 Type 1 (125% Specified Yield), ACI 318 Type 2 (Specified Tensile), ACI 349, ACI 359, AS3600, BS EN 1992-1-1, BS EN 1992-2, CAN/CSA - N287.2/.3/.4, DIN EN 1992-1-1, Eurocode 2, IBC Type 1 (125% Specified Yield), IBC Type 2 (Specified Tensile), ISO 15835, NEN EN 1992-1-1, NF A 35-020-1, NF EN 1992-1-1, ÖNORM EN 1992-1-1, Sellafeld Ltd. Std. ES_0_3110, US Army Corps of Engineers, CAN/CSA - A23.3



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN RAYCHEM SCHROFF TRACER