

ETL SELF-REGULATING HEATING CABLE



nVent RAYCHEM ETL self-regulating trace heating cables provide energy efficient pipe freeze protection. R-ETL-A/B are suitable for on- or in-pipe applications, R-ETL(-A/B)-CR for on-pipe only. Each are available in two power outputs (10 and 16 W/m at 5 °C), supported by a full range of heat shrinkable connections and accessories.

FEATURES

Simple to design, with fluoropolymer jacket option for use in pipes

Easy to install: small geometry, cut to length, meter marks

Energy efficient and safe: self-regulating cable, advanced energy saving controls, no overheating possible

Reliable during long life: 10 year product warranty available, maintenance free

SPECIFICATIONS

Nominal Thickness	5.8 mm
Nominal Width	8.5 mm
Min Bending Radius	10 mm
Max Continuous Exposure Temperature, Power Off	65 °C
Supply Voltage	220 – 240 V
Min Installation Temperature	-20 °C
Color	Black
Ground Path Type	Braid
Conductor Material	Nickel-Plated Copper

Catalog Number	Item Name	Nominal Power Output, In-Pipe @ 230V	Nominal Power Output @ 5°C, 230V	Max Circuit Length	Max Circuit Length, In-Pipe
924269-000	R-ETL-A	16 W/m	10 W/m	100 m	60 m
P000002042	R-ETL-B	25 W/m	16 W/m	100 m	60 m
P000002043	R-ETL-A-CR	W/m	10 W/m	100 m	m
P000002044	R-ETL-B-CR	W/m	16 W/m	100 m	m

ADDITIONAL PRODUCT DETAILS

Maximum circuit lengths are based on 230 VAC supply and C-Type characteristic circuit protection devices, switch-on at 5 °C.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

Nordamerika

Telefon +1.800.545.6258

Fax +1.800.527.5703

thermal.info@nvent.com

Europa Mellanösten, Afrika

Telefon + 32.16.213.51 1

Fax + 32.16.213.60 4

thermal.info@nvent.com

Stillahavs- Asien

Telefon +86.21.2412.1688

Fax +86.21.5426.3167

cn.thermal.info@nvent.com

Latinamerika

Telefon +1.713.868.4800

Fax +1.713.868.2333

thermal.info@nvent.com



Vår kraftiga portfölj av brännmärker:

nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF TRACER

nVent © 2022. Allt nVent märken, och logoer ägas, eller licenserat av nVent servar GmbH, eller dess ansluter. Alla andra varumärken är egenskapen av deras respektive ägare.

nVent reserverar ändringsspecifikationerna without märker rakt till.