

Klimaanlage SpectraCool Narrow Indoor/Outdoor, 2000 BTU 115 V, Hellgrau, Stahl

KATALOGNUMMER

N210216G050



SpectraCool Narrow Indoor/Outdoor Air Conditioners provide the same broad spectrum of cooling capacity and options and the SpectraCool Indoor/Outdoor units in a more narrow, space-saving solution for low-depth cabinet needs. Narrow models are designed to fit on 12-inch (300-mm) deep floor- and wall-mount enclosures.

SpectraCool Narrow with Advanced Corrosion Protection Compact Solutions provide industry leading corrosion protection to components critical to the performance of the air conditioner. For applications where air conditioners are exposed to harsh, corrosive, chemical elements. Hoffman utilizes advanced coatings to protect the critical components, extending their life and optimizing the extended performance level of the product.

Select units come with Remote Access Control (RAC), an integrated, parametric controller designed to work seamlessly with our enclosure air conditioner units for the purpose of remotely monitoring and managing anywhere from a single unit to an entire network of Spectra cool air conditioners from virtually anywhere in the world with a secure internet connection. Ensure that your systems are always running at optimal temperature levels, increase productivity and improve overall system reliability.

INDUSTRIE-STANDARDS

UL/cUL Listed; Type 12, 3R, 4; 4X optional; File No. SA6453

CE

IP 56 Internal Loop

IP 34 on External Loop

Telcordia GR-487 capable (Outdoor)

MERKMALE

Attraktives Industriedesign mit minimaler Verwendung sichtbarer Befestigungselemente.

Einfach zu montierende Flansche für problemlose Montage

Funktionstest jedes Geräts vor der Auslieferung

Zuverlässiger mechanischer Thermostat hinter dem Filter des Geräts

Narrow design accommodates 12-inch (300-mm) deep cabinets

Attractive industrial design with minimal use of visible fasteners

Level 2 Protection Include: Everything that was coated in Level 1, plus protective coatings applied to the evaporator (interior facing) side and an additional wrap around the thermostat

Cleanable, reusable aluminum mesh filter protects coils for maximum cooling performance

R407C, R513A or R134a refrigerants

Models for 115, 230 and 400/460 3-phase VAC power input

Outdoor model operating temperature range from -40 F/-40 C to 131 F/55 C (125 F/52 C on N28 Series)

Reliable mechanical thermostat on enclosure side of the unit; indoor air conditioner models include digital display on ambient side

Energy efficient rotary compressor on N36 and N43 models

PRODUKTMERKMALE

Nennkapazität BTU/h: 2000Btu/h

Nennleistung in Watt: 586W

Kältemittel: R513A

Korrosionsbeständig: Nein

Nennspannung: 115V

Anzahl Phasen: 1

Material: Baustahl

Oberfläche: Pulverbeschichtet

Farbe: Hellgrau

Dicke: 1.21mm

Höhe: 531mm

Breite: 254mm

Tiefe: 251mm

Betriebstemperatur: -40 to 55°C

Umgebungstemperatur: -40 to 55°C

Max. Stromstärke: 7A

Befestigung: Seitenwand

Installation Im Freien: Ja

Fernzugangskontrolle: Nein

Farbcode: RAL 7035

ZUSÄTZLICHE PRODUKTDDETAILS

Cutout Adapter options for enclosures with older nVent HOFFMAN or Competitive units for easy transitions to new air conditioners

For G52 400/460 rated voltage, the watts are based on .65 power factor.

WARNUNG

nVent-Produkte müssen in Übereinstimmung mit den Produktinformationsblättern und dem Schulungsmaterial von nVent installiert und verwendet werden. Informationsblätter sind verfügbar unter www.nVent.com sowie bei Ihrem nVent-Kundendienstvertreter. Unsachgemäße Installation, Missbrauch, Fehlanwendung oder andere Handlungen im Widerspruch zu den Anweisungen und Warnungen von nVent können zu Fehlfunktionen, Anlagenschäden, schwerer Körperverletzung sowie zum Tod führen und/oder haben die Annullierung der Garantie zur Folge.



Unser starkes markenportfolio:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE