

TYPE ENCLOSURE TYPES

DEFINITIONS PERTAINING TO NONHAZARDOUS LOCATIONS

Type 1 EnclosuresType 1 enclosures are intended for indoor use primarily to provide a degree of protection

against limited amounts of falling dirt.

Type 2 EnclosuresType 2 enclosures are intended for indoor use primarily to provide a degree of protection

against limited amounts of falling water.

Type 3 EnclosuresType 3 enclosures are intended for outdoor use primarily to provide a degree of protection

against rain, sleet, windblown dust, and damage from external ice formation.

Type 3R EnclosuresType 3R enclosures are intended for outdoor use primarily to provide a degree of protection

against rain, sleet, damage from external ice formation, and must have a drain hole.

Type 3S EnclosuresType 3S enclosures are intended for outdoor use primarily to provide a degree of protection

against rain, sleet, windblown dust, and to provide for operation of external mechanisms when

ice laden.

Type 4 EnclosuresType 4 enclosures are intended for indoor or outdoor use primarily to provide a degree of

protection against windblown dust and rain, splashing water, hose-directed water, and damage

from external ice formation.

Type 4X EnclosuresType 4X enclosures are intended for indoor or outdoor use primarily to provide a degree of

protection against corrosion, windblown dust and rain, splashing water, hose-directed water,

and damage from external ice formation.

Type 5 EnclosuresType 5 enclosures are intended for indoor use primarily to provide a degree of protection

against airborne dust, falling dirt, and dripping noncorrosive liquids.

Type 6 EnclosuresType 6 enclosures are intended for indoor or outdoor use primarily to provide a degree of

protection against hose-directed water, the entry of water during temporary submersion at a

limited depth, and damage from external ice formation.

Type 6P EnclosuresType 6P enclosures are intended for indoor or outdoor use primarily to provide a degree of

protection against hose-directed water, the entry of water during prolonged submersion at a

limited depth, and damage from external ice formation.

Type 12 EnclosuresType 12 enclosures are intended for indoor use primarily to provide a degree of protection

against circulating dust, falling dirt, and dripping noncorrosive liquids.

Type 12K EnclosuresType 12K enclosures with knockouts are intended for indoor use primarily to provide a degree

of protection against circulating dust, falling dirt, and dripping noncorrosive liquids.

Type 13 EnclosuresType 13 enclosures are intended for indoor use primarily to provide a degree of protection

against dust, spraying of water, oil, and noncorrosive coolant.

DEFINITIONS PERTAINING TO HAZARDOUS (CLASSIFIED) LOCATIONS

Type 7 enclosures are intended for indoor use in locations classified as Class I, Groups A, B, C, or Type 7 En closures

D, as defined in the National Electrical Code.

Type 8 Enclosures Type 8 enclosures are intended for indoor or outdoor use in locations classified as Class I,

Groups A, B, C, or D, as defined in the National Electrical Code.

Type 9 enclosures are intended for indoor use in locations classified as Class II, Groups E, F, and **Type 9 Enclosures**

G, as defined in the National Electrical Code*.

Type 10 enclosures are constructed to meet the applicable requirements of the Mine Safety and **Type 10 Enclosures**

Health Administration.

ENCLOSURE TYPES VS. IEC CLASSIFICATION DESIGNATION COMPARISON

| Enclosure Type rating | IEC Enclosure (IP) Classification |
|-----------------------|-----------------------------------|
| 1 | IP 10 |
| 2 | IP 11 |
| 3 | IP 54 |
| 3R | IP 14 |
| 3S | IP 54 |
| 4 and 4X | IP 55 |
| 5 | IP 52 |
| 6 and 6P | IP 67 |
| 12 and 12K | IP 52 |
| 13 | IP 54 |
| (one way conversion) | |

Note: This table is for the reference only. (Direct conversion is not allowed) Both enclosure type rating test and IEC enclosure (IP) rating test have to be tested to achieve both rating.

North America

Tel +1.800.545.6258 Fax +1.800.527.5703 thermal.info@nvent.com **Europe, Middle East, Africa**

Tel +32.16.213.511 Fax +32.16.213.604 thermal.info@nvent.com **Asia Pacific**

Tel +86.21.2412.1688 Fax +86.21.5426.3167 cn.thermal.info@nvent.com **Latin America**

Tel +1.713.868.4800 Fax +1.713.868.2333 thermal.info@nvent.com



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

RAYCHEM

SCHROFF

TRACER

^{*} Refer to NEMA Standards Publication No. 250 Enclosures for Electrical equipment (1000 Volts Maximum) or other third party certification standards for specific requirements for product construction, testing and performance such as Underwriters Laboratories, Inc., Standard UL 50 "Standards for Enclosures for Electrical Equipment," and UL886 "Outlet Boxes and Fittings for use in Hazardous (Classified) Locations."