

CONNECT AND PROTECT

nVent ERICO Cadweld Welded High-Voltage Power Connections

For Underground and Subsea Cable Splicing


nVent

ERICO


TABLE OF CONTENTS

INTRODUCTION	2 – 3
CADWELD HIGH-VOLTAGE WELDING PROCESS	4
CADWELD ELECTRICAL & MECHANICAL PERFORMANCE.....	5
CADWELD WELDING EQUIPMENT.....	6
EASY TO MAKE CADWELD CONNECTIONS.....	7
PRODUCT OVERVIEW ALUMINUM A22 WELDS	8
PRODUCT OVERVIEW COPPER F20 WELDS.....	9
IMPORTANT NOTES	10 – 11

nVent Engineered Electrical & Fastening Solutions is a leading global manufacturer and marketer of superior engineered products for niche electrical, mechanical and concrete applications. These nVent products are sold globally under a variety of market-leading brands: nVent ERICO welded electrical connections, facility electrical protection, and rail and industrial products; nVent CADDY fixing, fastening and support products; nVent ERIFLEX low voltage power and grounding connections; and nVent LENTON engineered systems for concrete reinforcement.

For more information please visit nVent.com/ERICO.

INTRODUCTION



BETTER THAN MECHANICAL CONNECTIONS AND LESS LABOR AND COST INTENSIVE THAN MIG OR TIG.

Cadweld high-voltage welds are permanent molecular bonds that cannot loosen or deteriorate, no maintenance is required and no resistance increase over time, so there is a continuous optimal electrical path. This makes Cadweld connections superior to traditional compression or mechanical connections that provide only surface contact between conductors and a less-than-perfect current path. In addition, Cadweld high-voltage welding system is easier to use and lower in labor cost, since you don't need a certified welder.

Full on site training can be provided by nVent Engineers.

A LOW EMISSION PROCESS

Cadweld high-voltage welding set-up uses a unique ceramic fiber smoke filter system which prevents sparks and produces minimal smoke, but also reduces dust and other emissions to an acceptable level for exposures, even if used in unventilated small rooms and cable tunnels.

Cadweld High-Voltage Welding Process

CADWELD WELDING IS A RELIABLE METHOD OF QUICKLY MAKING ELECTRICAL CONNECTIONS.

Optimum Standardization:

Welding equipment (crucible, smokefilter body, frames, etc.) is standardized and can be used on all connections. Only different molds and different types of welding material are needed for Copper or for Aluminum welds.

Cadweld connections give you a single process for making all cable-to-cable, splices and terminations, tubular bus and flat bus connections.

Two different welding material options allow Cu-Cu as well as Al-Al and Al-Cu* connections.


The welding material contains either copper and aluminum oxide or aluminum and calcium sulfate, both with additional ingredients.

The ignitor starts an exothermic reaction inside the crucible, producing the molten copper or molten aluminum. The molten material then flows from the crucible into the mold, welding the ends of the conductors to create the molecular bond.



CADWELD HIGH-VOLTAGE SYSTEM ADVANTAGES:

- Cadweld high-voltage welding system will weld the following materials:
 - Standard Al or Cu cable (concentric)
 - Segmented Al or Cu cable (milican)
 - Solid Al or Cu cable
- Cadweld connections can be made easily with minimal training.
- Cadweld weld is small – only 70 mm of insulation is removed from each cable end and therefore is easy to re-insulate.
- Specially designed weld profile for high-voltage applications.
- No external power or heat source required.
- Has a current carrying capacity equal to that of the conductor.
- Permanent molecular bond will not deteriorate with age, cannot loosen or corrode.
- Will withstand repeated faults, is made with lightweight equipment, has low labor cost and is time saving on jobsites.



*For Al-Cu connections, Copper must be tinned.

Cadweld Electrical & Mechanical Performance

TECHNICAL INFORMATION:

Strength Results

In laboratory tests, the tensile strength of Cadweld high-voltage cable connections proved to have overall strong results. The tests show on average that the Cadweld connection provides about 75% tensile strength compared to the cable by itself. Test results vary between approx. 60% up to 90% tensile strength, whereby the breaking point is annealed cable at the edge of the Cadweld weld.

Performance Results

Like all Cadweld connections, their permanent low resistivity provides a current-carrying capacity that's greater than the conductors.

PERFORMANCE RESULTS

Aluminum Conductor		Resistance in $\mu\Omega$
Cable		
Cable-to-Cable Connection	A22	64.01
Cable Only		64.43

RANGE OF CAPABILITIES

Conductor	Conductor Range	Connection Application
Al-cable to Al-cable or solid cable	17 mm / 56 mm diameter	<ul style="list-style-type: none"> • High-, medium- and low-voltage • High current electrical • Earthing
Cu-cable or Al-cable to Cu-cable	17 mm / 64 mm diameter	<ul style="list-style-type: none"> • High-, medium- and low-voltage • High current electrical • Earthing
Al-solid cable, -lug, busbar or flexible connections in Al-Al or Al-Cu	Customized to meet application	<ul style="list-style-type: none"> • High current • Electrical connections for electrolysis and chemical plants

*Other cable sizes and combinations also available, please contact your nVent engineer.

CONNECTION EXAMPLES:




Terminations: Copper 'Top Bolt' on Aluminum solid cable



Connection between two Aluminum cables



Cadweld Welding Equipment




Cadweld molds are produced from graphite blocks and can be used for 50 or more welds. Molds for Al-Al and Al-Cu are different from Cu-Cu molds. Frames are needed in order to close the mold and hold it. Mold Sealer is required around the cable on the outside of the Cadweld mold to prevent leakage of molten weldmetal.



Cadweld crucibles are included in the mold design for smaller conductor diameters. Large welds will require a separate crucible in order to accept the required amount of welding material. Frames are needed in order to close the crucible and hold it.



Cadweld high-voltage connection set-up uses a unique ceramic fiber smoke filter system which prevents sparks and produces minimal smoke. Filters can be used only once, but replacement filter sets are available for both sizes of smokefilter box.



Cadweld Gap device is a tool to correctly “gap” and center the cable ends. The tool kit provides brushes and other items which are used for easy cleaning of conductors before making connections. Cadweld Air-Dry Flux T327A is used on Al-Al and Al-Cu connections immediately after cleaning the aluminum conductors with the brush. Cadweld Air-Dry Flux must be lightly sprayed on to prevent re-oxidation.



Cadweld welding material is a mixture of copper, aluminum and other ingredients. Each bag or container contains sufficient welding material for the specified connection. Cadweld welding material cannot ignite spontaneously. It can be handled and stored without danger. Adding starting material to the welding material is necessary to begin the exothermic reaction.


Easy To Make Cadweld Connections

BEFORE WELDING: READ, UNDERSTAND AND FOLLOW ALL SAFETY INSTRUCTIONS PACKAGED WITH YOUR MOLD!




1

- Dry the mold and the conductors
- Clean the conductors
- Place cable ends in the mold




2

- Correctly "gap" and center cable ends
- Close the handles to lock the mold
- Drop the metal disk into the mold




3

- Dump the welding material into the mold
- Sprinkle the starting material over the welding material and onto the lip of the mold (different for larger conductor sizes – follow instruction packaged with your mold)



4

- Attach and fit the smokefilter box and ignite
- Open the mold after approximately 5 minutes when material has solidified
- Remove the mold from completed weld



5

- A completed Cadweld connection
- Will not loosen or increase resistance over lifetime of installation

Detailed instructions and safety precautions are provided with every Cadweld mold. **You must read and understand all instructions before making a connection.** If you have any questions, please contact an nVent engineer for assistance. Instruction sheets are also available for download at nVent.com/ERICO.

Product Overview Aluminum A22 Welds

Cable Ø (mm)		MOLD			CRUCIBLE		SMOKEFILTER		GAP	TOOL	AI-	Welding Material	Star-
from	to	Type	Frame	Sealer	Type	Frame	House	Set	Device	KIT	FLUX	Code (Gramms)	Ignitor
17.1	18.0	S1V18M	FM-102-SR	T403	--NR--	--NR--	SF-102-SR	SFS-102-F20-SR	CL-GD-3	TS-SR	T327A	300A22	Yes
18.1	19.0	S1V19M										300A22	
19.1	20.0	S1V20M										300A22	
20.1	21.0	S1V21M										300A22	
21.1	22.0	S1V22M										400A22	
22.1	23.0	S1V23M										400A22	
23.1	24.0	S1V24M										400A22	
24.1	25.0	S1V25M										400A22	
25.1	26.0	S1V26M										400A22	
26.1	27.0	S1V27M										500A22	
27.1	28.0	S1V28M										500A22	
28.1	29.0	S1V29M										500A22	
29.1	30.0	S1V30M										500A22	
30.1	31.0	S1V31M										500A22	
31.1	32.0	S1V32M										600A22	
32.1	33.0	S1V33M										700A22	
33.1	34.0	S1V34M			800A22								
34.1	35.0	S1V35M			800A22								
35.1	36.0	S1V36M			800A22								
36.1	37.0	S1V37M			800A22								
37.1	38.0	S1V38M			1000A22								
38.1	39.0	S1V39M			1000A22								
39.1	40.0	S1V40M			1000A22								
40.1	41.0	S1V41M			1000A22								
41.1	42.0	S1V42M			1100A22								
42.1	43.0	S1V43M			1100A22								
43.1	44.0	S1V44M			1100A22								
44.1	45.0	S1V45M			1200A22								
45.1	46.0	S1V46M			1200A22								
46.1	47.0	S1V47M			1300A22								
47.1	48.0	S1V48M			1300A22								
48.1	49.0	S1V49M			1400A22								
49.1	50.0	S1V50M	1400A22										
50.1	51.0	S1V51M	1400A22										
51.1	52.0	S1V52M	1400A22										
52.1	53.0	S1V53M	1400A22										
53.1	54.0	S1V54M	1700A22										
54.1	55.0	S1V55M	1900A22										
55.1	56.0	S1V56M	2000A22										

Notes:

- For AI-CU connections, copper cable or termination must be tinned
- Cadweld A22 welds (AI-AI / AI-CU) are for indoor use only
- All A22 welds require AI-FLUX
- Standard range shown, for different sizes/combinations please contact an nVent engineer




Product Overview Copper F20 Welds

Cable Ø (mm)		MOLD Type	Frame	Sealer	CRUCIBLE		SMOKEFILTER		GAP Device	TOOL KIT	Welding Material Code	Star-Ignitor			
from	to				Type	Frame	House	Set							
17.1	18.0	SS-18-SR	FM-102-SR	T403	--N/N--		SF-102-SR	SFS-102-F20-SR	CL-GD-3	TS-SR	P98F20	Yes			
18.1	19.0	SS-19-SR									P98F20				
19.1	20.0	SS-20-SR									P98F20				
20.1	21.0	SS-21-SR									P99F20				
21.1	22.0	SS-22-SR									P99F20				
22.1	23.0	SS-23-SR									P99F20				
23.1	24.0	SS-24-SR									P99F20				
24.1	25.0	SS-25-SR									P99F20				
25.1	26.0	SS-26-SR									P100F20				
26.1	27.0	SS-27-SR									P100F20				
27.1	28.0	SS-28-SR									P100F20				
28.1	29.0	SS-29-SR									P100F20				
29.1	30.0	SS-30-SR									P101F20				
30.1	31.0	SS-31-SR									P101F20				
31.1	32.0	SS-32-SR									P101F20				
32.1	33.0	SS-33-SR									P101F20				
33.1	34.0	SS-34-SR									P101F20				
34.1	35.0	SS-35-SR									P101F20				
35.1	36.0	SS-36-SR									P103F20				
36.1	37.0	SS-37-SR									P103F20				
37.1	38.0	SS-38-SR									P103F20				
38.1	39.0	SS-39-SR									P104F20				
39.1	40.0	SS-40-SR									P104F20				
40.1	41.0	SS-41-SR									P104F20				
41.1	42.0	SS-42-SR			P104F20										
42.1	43.0	SS-43-SR			P105F20										
43.1	44.0	SS-44-SR			P105F20										
44.1	45.0	SS-45-SR			P105F20										
45.1	46.0	SS-46-SR			P105F20										
46.1	47.0	SS-47-SR			P105F20										
47.1	48.0	SS-48-SR			P105F20										
48.1	49.0	SS-49-SR			P106F20										
49.1	50.0	SS-50-SR			P106F20										
50.1	51.0	SS-51-SR			P106F20										
51.1	52.0	SS-52-SR			P107F20										
52.1	53.0	SS-53-SR			P107F20										
53.1	54.0	SS-54-SR			P108F20										
54.1	55.0	SS-55-SR			P108F20										
55.1	56.0	SS-56-SR			P108F20										
56.1	57.0	SS-57-SR			P108F20										
57.1	58.0	SS-58-SR			P108F20										
58.1	59.0	SS-59-SR			P110F20										
59.1	60.0	SS-60-SR			P110F20										
60.1	61.0	SS-61-SR			P110F20										
61.1	62.0	SS-62-SR			P110F20										
62.1	63.0	SS-63-SR			P110F20										
63.1	64.0	SS-64-SR			P110F20										
							CR-158-128-SR	FC-158-SR	SF-158-SR		SFS-158-F20-SR		CL-GD-6		


Notes:

- For horizontal straight splice or termination to 'Top Bolt' connections
- Cadweld F20 molds require Mold Sealer
- Molds make approx. 60 connections/welds
- Standard range shown, for different sizes/combinations please contact an nVent engineer



IMPORTANT NOTES



nVent offers welding material for different conductors. Please note that any Al-Cu or Al-Al connections require Cadweld A22 welding material. Cu-Cu connections will be processed with Cadweld F20 welding material.




To provide a reliable connection between Al and Cu, the Cadweld welding process will require only tinned copper conductors.



Immediately after cleaning aluminium conductors, use Cadweld Air Dry Flux T327A to prevent re-oxidation of the cleaned aluminium surface. There is no requirement to use Cadweld Air Dry Flux on copper conductors.


BEFORE WELDING: Read, understand and follow all safety instructions packaged with your mold. Refer to instruction sheet IP 8067-A, which is also available at nVent.com/ERICO for download.

IMPORTANT NOTES




Please make sure that you maintain the correct “gap” between conductors inside the mold. This will allow the molten welding material to flow and connect the conductor. The number of the GAP Device shown on product overview pages 8 & 9 indicates the correct “gap”.

If you are not sure or have additional questions, please contact an nVent engineer prior to any welding operation.



Apply (mold) sealer T403 between the mold and conductor to prevent leaking molten weld material.



Remove risers and overflow at the Cadweld weld once material is solidified.

BEFORE WELDING: Read, understand and follow all safety instructions packaged with your mold. Refer to instruction sheet IP 8067-A, which is also available at nVent.com/ERICO for download.

Our powerful portfolio of brands:

CADDY ERICO HOFFMAN RAYCHEM SCHROFF TRACER



[nVent.com/ERICO](https://www.nvent.com/ERICO)

WARNING: nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [nVent.com/ERICO](https://www.nvent.com/ERICO) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and/or death, and void your warranty.

©2018 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

Erico-SB-PN1740B-I383LT10WWEN-EN-1805