

VIA-DU-20 CONTROL UNIT



nVent RAYCHEM VIA-DU-20 is an energy efficient control unit for ramp heating, surface snow melting and de-icing applications. Equipped with ground temperature and moisture sensors, the system is only energised when these are both activated. An optional ambient temperature sensor is available, for identifying risk of freezing rain.

FEATURES

Simple and fast to install and operate

Energy saving: circuits energized only when ground temperature and moisture sensors are activated

BMS connection and alarm contacts for remote alarm function

Reliable during long life: 6 year extended product warranty available, maintenance free

SPECIFICATIONS

Catalog Number	Item Name	IP Rating	Sensor Type	Pavement Moisture Sensor	Adjustment Range, Frost Protection	Power Consumption, Standby	Height	Width	Depth
599514-000	VIA-DU-20	IP65	Remote Sensor	Yes	1 – 6 °C	5 W	54 mm	190 mm	58 mm

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

Tel +1.800.545.6258

Fax +1.800.527.5703

thermal.info@nvent.com

Europe, Middle East, Africa

Tel +32.16.213.511

Fax +32.16.213.604

thermal.info@nvent.com

Asia Pacific

Tel +86.21.2412.1688

Fax +86.21.5426.3167

cn.thermal.info@nvent.com

Latin America

Tel +1.713.868.4800

Fax +1.713.868.2333

thermal.info@nvent.com



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF TRACER

© 2022 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners.

nVent reserves the right to change specifications without notice.