

nVent LENTON Lock Coupler Transition Chart

METRIC REBAR

Standard nVent LENTON LOCK is designed to be used for single-step transitions and in many cases multi-step transitions.

Rebar Size	LL12B1MG	LL16B1MG	LL20B1MG	LL22B1MG	LL25B1MG	LL28B1MG	LL32B1MG	LL36S1MG
	LL12S1MG	LL16S1MG	LL20S1MG	LL22S1MG	LL25S1MG	LL28S1MG	LL32S1MG	
10 mm	✓	-	-	-	-	-	-	-
12 mm	✓	✓	-	-	-	-	-	-
14 mm	-	✓	-	-	-	-	-	-
16 mm	-	✓	✓	-	-	-	-	-
18 mm	-	-	✓	-	-	-	-	-
20 mm	-	-	✓	✓	✓	-	-	-
22 mm	-	-	-	✓	✓	-	-	-
24 mm	-	-	-	-	✓	✓	✓	-
25 mm	-	-	-	-	✓	✓	✓	-
26 mm	-	-	-	-	✓	✓	✓	-
28 mm	-	-	-	-	-	✓	✓	-
30 mm	-	-	-	-	-	✓	✓	-
32 mm	-	-	-	-	-	-	✓	✓
34 mm	-	-	-	-	-	-	-	✓
36 mm	-	-	-	-	-	-	-	✓

✓ Indicates which rebar sizes can be used in each coupler.

The higher-performing nVent LENTON LOCK B-series coupler can be substituted in place of the nVent LENTON LOCK S-series.

Please contact nVent LENTON or visit www.nVent.com/LENTON for specific questions regarding regional availability, approvals or performance requirements.

