


E507S-2LS-2



DOUBLE-POLE LINE-SENSING THERMOSTAT FOR HAZARDOUS LOCATIONS







PRODUCT OVERVIEW

The nVent RAYCHEM E507S-2LS-2 thermostat is designed to control heat-tracing systems in hazardous locations. The thermostat functions as a double-pole single-throw (DPST) switch, opening and closing the electrical connection to both heating cable bus wires.

The E507S-2LS-2 senses pipe or tank wall temperatures and is used to control one heat-tracing circuit directly.

SPECIFICATIONS

Enclosure TYPE 4, 7, 9, lacquer-coated

cast-aluminum housing, stainless

steel hardware

Entries One 3/4-in NPT conduit hub Set point range 25°F to 325°F (-4°C to 163°C) Sensor exposure

Housing exposure

-40°F to 420°F (-40°C to 215°C)

-40°F to 140°F (-40°C to 60°C)

limits

DPST Switch

Electrical rating 22 A at 208 / 240 Vac Relay coil 208-240 Vac, 4 VA

Accuracy ±6°F (±3.3°C)

Deadband 2°F to 12°F (1.1°C to 6.7°C) above

actuation temperature

Set point repeatability Sensor type

±3°F (±1.7°C)

Fluid-filled (silicone) bulb and 9 ft (2.7 m) capillary

300 series stainless steel Sensor material Connection Screw terminals, 10-14 AWG

terminals $(2-5 \text{ mm}^2)$

APPROVALS

Hazardous Locations







Class I. Div. 1 and 2. Groups B. C. D. Class II, Div. 1 and 2, Groups E, F, G Class III

Raychem-DS-H55206-E507S2LS2-EN-1805 nVent.com | 1

North America

Tel +1.800.545.6258 Fax +1.800.527.5703 thermal.info@nvent.com

Europe, Middle East, Africa

Tel +32.16.213.511 Fax +32.16.213.603 thermal.info@nvent.com

Asia Pacific

Tel +86.21.2412.1688 Fax +86.21.5426.3167 cn.thermal.info@nvent.com

Latin America

Tel +1.713.868.4800 Fax +1.713.868.2333 thermal.info@nvent.com



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN RAYCHEM SCHROFF TRACER