

CSBQIKCSE

Quick Grip Lateral Sway Brace


Part Number***	Service Pipe Size		UL® Load Rating		**FM® Load Rating		
			*Lightwall	Schedule 10/40	*Lightwall	Schedule 10	Schedule 40
	INCH	mm	lbs. (N)	lbs. (N)	lbs. (N)	lbs. (N)	lbs. (N)
CSBQIKCSE0250(XX)	2 1/2	62.5	2015 (8960)	2015 (8960)	N/A	N/A	N/A
CSBQIKCSE0300(XX)	3	75	2015 (8960)	2015 (8960)	N/A	N/A	N/A
CSBQIKCSE0400(XX)	4	100	2015 (8960)	2015 (8960)	3000 (13340)	3000 (13340)	3000 (13340)
CSBQIKCSE0500(XX)	5	125	N/A	2015 (8960)	N/A	2100 (9340)	2600 (11560)
CSBQIKCSE0600(XX)	6	150	2015 (8960)	2015 (8960)	2100 (9340)	2100 (9340)	2600 (11560)
CSBQIKCSE0800(XX)	8	200	N/A	2015 (8960)	N/A	2200 (9785)	2400 (10675)

*** (XX) = Finish Specifier

*UL Listed with Lightwall (Commonly referred to as Schedule 7) - Sizes 2.5, 3, 4" with DYNA-FLOW®, Size 6" with EZ FLOW™

**FM Load rating for Schedule 10 may be applied to GB/T 3091, GB/T 3092 and FM Approved Thinwall pipe.
FM Approved with 1" or 1-1/4" Schedule 40 or GB/T 3091 brace pipe.
FM Load rating for Lightwall may also be applied to GB/T 8163 pipe.

For Nominal Pipe Sizes : 4, 5, 6, 8



①



②



Sway brace assemblies are intended to be installed in accordance with NFPA®-13 and the manufacturer's installation instructions.

WARNING:

1. ERICO products shall be installed and used only as indicated in ERICO product instruction sheets and training materials. Instruction sheets are available at www.erico.com and from your ERICO customer service representative.
2. ERICO products must never be used for a purpose other than the purpose for which they were designed or in a manner that exceeds specified load ratings.
3. All instructions must be completely followed to ensure proper and safe installation and performance.
4. Improper installation, misuse, misapplication or other failure to completely follow ERICO's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death.
5. Products that are manufactured using spring steel components shall be used only in a non-corrosive indoor environment.
6. All pipe supports, hangers, intermediate components and structural attachments must ONLY be used as described herein and are NEVER to be used for any other purpose.

The customer is responsible for:

- a. Conformance to all governing codes.
- b. The integrity of structures to which the products are attached, including their capability of safely accepting the loads imposed, as evaluated by a qualified engineer.
- c. Using appropriate industry standard hardware as noted above.

SAFETY INSTRUCTIONS:

All governing codes and regulations and those required by the job site must be observed.
Always use appropriate safety equipment such as eye protection, hard hat, and gloves as appropriate to the application.

DYNA-FLOW is a registered trademark of Allied Tube and Conduit Corporation.

EZ FLOW is a trademark of Northwest Pipe Company.

FM is a registered certification mark of FM Approvals LLC, LTD.

NFPA is a registered trademark of National Fire Protection Association.

UL is a registered trademark of Underwriters Laboratories, Inc.

CADDY, CADWELD, CRITEC, ERICO, ERIFLEX, ERITECH, and LENTON are registered trademarks of ERICO International Corporation.

TECHNICAL SUPPORT:
www.erico.com

CFS404_E

1 OF 2

© 2009, 2011 ERICO International Corporation


ERICO®



CSBQIKCSE

Quick Grip Lateral Sway Brace

For Nominal Pipe Sizes : 4, 5, 6, 8 cont.



For Nominal Pipe Sizes : 2 1/2, 3

