



# BC-P CONDUIT TO BEAM CLAMP



## FEATURES

Easy installation to beam flanges

Eliminates offset bending conduit


## SPECIFICATIONS

**Finish** nVent CADDY Armour

**Material** Spring Steel

Catalog Number	EMT Conduit Size	Rigid Conduit Size	Outer Diameter(OD)	Torque(TQ)	Ultimate Static Load(F)
BC8P	1/2"			20 ft lb	25 lb
BC12P	3/4"	1/2"		20 ft lb	25 lb
BC16P	1"	3/4"	1.181" – 1.378"	20 ft lb	25 lb

## DIAGRAMS



## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials.

Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

**North America**

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical Support

**Europe**

Netherlands:

+31 800-0200135

France:

+33 800 901 793

**Europe**

Germany:

800 1890272

Other Countries:

+31 13 5835404

**APAC**

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

**nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF TRACER**

© 2022 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners.

nVent reserves the right to change specifications without notice.