



# NVENT CADDY CAT HP J-HOOK WITH HAMMER-ON FLANGE CLIP



## CERTIFICATIONS



## FEATURES

Requires only a hammer to install

Provides optimal support for high-performance data cable, up to and including Cat 5e, Cat 6, Cat 6A, Cat 7 and fibre optic

Provides superior fill capacity and load rating over most other non-continuous cable support alternatives

Rounded edges on J-Hooks provide proper bend radius support for high performance data cables

Cost effective alternative to expensive cable tray

Complies with EN 50174-2

Meets ISO®/IEC 14763-2, ANSI®/TIA 568 and ANSI®/TIA 569

## SPECIFICATIONS

**Finish** Pregalvanized;nVent CADDY Armour

**Material** Steel;Spring Steel

Catalog Number	Diameter(Ø)	Area	Cable Capacity, Cat 5e	Cable Capacity, Cat 6	Cable Capacity, Cat 6A	Flange Thickness(FT)	Static Load(F)
CAT16HP24SM	1"	1.07 in <sup>2</sup>	20	15	10	1/8" – 1/4"	60 lb
CAT21HP24SM	1 5/16"	2.29 in <sup>2</sup>	50	40	25	1/8" – 1/4"	60 lb
CAT32HP24SM	2"	3.97 in <sup>2</sup>	90	60	35	1/8" – 1/4"	60 lb
CAT48HP24SM	3"	9.26 in <sup>2</sup>	200	150	80	1/8" – 1/4"	60 lb


Catalog Number	Diameter( $\emptyset$ )	Area	Cable Capacity, Cat 5e	Cable Capacity, Cat 6	Cable Capacity, Cat 6A	Flange Thickness(FT)	Static Load(F)
CAT64HP24SM	4"	15.48 in <sup>2</sup>	330	220	140	1/8" – 1/4"	60 lb
CAT16HP58SM	1"	1.07 in <sup>2</sup>	20	15	10	5/16" – 1/2"	60 lb
CAT21HP58SM	1 5/16"	2.29 in <sup>2</sup>	50	40	25	5/16" – 1/2"	60 lb
CAT32HP58SM	2"	3.97 in <sup>2</sup>	90	60	35	5/16" – 1/2"	60 lb
CAT48HP58SM	3"	9.26 in <sup>2</sup>	200	150	80	5/16" – 1/2"	60 lb
CAT64HP58SM	4"	15.48 in <sup>2</sup>	330	220	140	5/16" – 1/2"	60 lb
CAT16HP912SM	1"	1.07 in <sup>2</sup>	20	15	10	1/2" – 3/4"	60 lb
CAT21HP912SM	1 5/16"	2.29 in <sup>2</sup>	50	40	25	1/2" – 3/4"	60 lb
CAT32HP912SM	2"	3.97 in <sup>2</sup>	90	60	35	1/2" – 3/4"	60 lb
CAT48HP912SM	3"	9.26 in <sup>2</sup>	200	150	80	1/2" – 3/4"	60 lb
CAT64HP912SM	4"	15.48 in <sup>2</sup>	330	220	140	1/2" – 3/4"	60 lb

## ADDITIONAL PRODUCT DETAILS

Non-continuous supports may not exceed spacing of 5' (1.5 m) per TIA 569-C.9.7 and EN 50174-2.

Cable capacity is calculated based on a 70% fill rate.

## DIAGRAMS



## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

**North America**

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical Support

**Europe**

Netherlands:

+31 800-0200135

France:

+33 800 901 793

**Europe**

Germany:

800 1890272

Other Countries:

+31 13 5835404

**APAC**

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:  
**nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF TRACER**

© 2022 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners.

nVent reserves the right to change specifications without notice.