



PUSH IN CONDUIT CLAMP



FEATURES

Push-in installation of conduit

Eliminates need for offset bending conduit

May be used for either vertical or horizontal installations


SPECIFICATIONS

Finish nVent CADDY Armour

Material Spring Steel

Catalog Number	EMT Conduit Size	Outer Diameter(OD)	Hole Size(HS)	Hole Type	Ultimate Static Load 1(F1)	Ultimate Static Load 2(F2)
12P4I	3/4"	0.866" Min, 1.181" Max, 0.752" Nom	1/4"	Threaded	25 lb	15 lb
16P4I	1"	1.181" Min, 1.378" Max, 1.000" Nom	1/4"	Threaded	25 lb	15 lb
8P4I	1/2"	0.709" – 0.866"	1/4"	Threaded	25 lb	15 lb
12P	3/4"	0.866" – 1.181"	9/32"	Plain	25 lb	15 lb
16P	1"	1.181" – 1.378"	9/32"	Plain	25 lb	15 lb
8P	1/2"	0.709" – 0.866"	9/32"	Plain	25 lb	15 lb

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
 Option 1 – Customer Care
 Option 2 – Technical Support

Europe

Netherlands:
 +31 800-0200135
 France:
 +33 800 901 793

Europe

Germany:
 800 1890272
 Other Countries:
 +31 13 5835404

APAC

Shanghai:
 + 86 21 2412 1618/19
 Sydney:
 +61 2 9751 8500



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF TRACER

© 2022 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners.

nVent reserves the right to change specifications without notice.