



STRUT SEISMIC HINGE BRACKET ASSEMBLY



CERTIFICATIONS



FEATURES

Used for installations where strut brace is parallel to structure

One wrench size fits all required hardware, eliminating the need to change tools

Shear-off head helps ensure correct torque and simplifies inspection


SPECIFICATIONS

Finish Electrogalvanized

Material Steel

Catalog Number	Hole Size(HS)	Width(W)	Thickness(T)	A	B
CSBUS1PA	9/16"	1.600"	1/4"	7"	1.880"
CSBUS2PA	13/16"	1.600"	1/4"	7"	1.880"

DIAGRAMS



FM Loads					
Part Number	Brace Member	Horizontal Capacity per Installation Angle from Vertical			
		30° - 44°	45° - 59°	60° - 74°	75° - 90°
CSBUS1PA	12 GA Strut Channel	1,162 lb	1,864 lb	1,864 lb	1,680 lb
CSBUS2PA	12 GA Strut Channel	1,162 lb	1,864 lb	1,864 lb	1,680 lb

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF TRACER

© 2022 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners.

nVent reserves the right to change specifications without notice.