

# COPPER-BONDED GROUND ROD, TWO PIGTAILS



## FEATURES

Assembly for use on wooden utility poles

Anti-copper theft application


Conductors exothermically welded to ground rod with nVent ERICO Cadweld, then the connection is covered with heat shrink wrap

Complete assembly covered in black insulation

## SPECIFICATIONS

Catalog Number	Material	Tensile Strength	Insulated	Ground Rod Diameter, Nominal	Ground Rod Diameter, Actual(Ø)	Length 1(L1)	Length 2(L2)	Plating Thickness	Conductor Size	Unit Weight
615800CW0505	Copper-Bonded Steel	80,000 psi Min	Yes	5/8"	0.560"	10'	1.640'	10 mil	70 mm <sup>2</sup>	10.400 lb

## DIAGRAMS



## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

**⚠ WARNING:** This product can expose you to chemicals including nickel, which is known to the State of California to cause

cancer and birth defects or other reproductive harm. For more information go to [www.P65Warnings.ca.gov](http://www.P65Warnings.ca.gov).

**North America**

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical Support

**Europe**

Netherlands:

+31 800-0200135

France:

+33 800 901 793

**Europe**

Germany:

800 1890272

Other Countries:

+31 13 5835404

**APAC**

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:  
**nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF TRACER**

© 2022 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners.

nVent reserves the right to change specifications without notice.