

MODULAR TDX PANEL PROTECTOR, 100 KA, 277/480 V UN, 3PH 4W+G DISTRIBUTION SYSTEM

CATALOG NUMBER

TDX100M277480



CERTIFICATIONS



FEATURES

Transient Discriminating (TD) Technology provides increased service life

Modular design allows easy replacement of surge modules

Built-in features include TD Technology, thermal protection and short circuit current fusing

Compact NEMA®-4 enclosure design can be flush mounted or installed in a small space

Status indication flag per mode, voltage presence LEDs, audible alarm and voltage-free contacts providing remote status monitoring

100 kA 8/20 μ s maximum surge rating provides protection suitable for main-distribution panels and an extended operational life

PRODUCT ATTRIBUTES

Nominal System Voltage (Un): 277/480 V

Distribution System: 3Ph 4W+G

Max Continuous Operating Voltage (Uc): 320/550 VAC

Stand-off Voltage: 480/831 VAC

Frequency: 50 – 60 Hz

Protection Modes: L-N;L-PE;N-PE

Short Circuit Current Rating (SCCR): 200 kA

Nominal Discharge Current (In), IEC: 40 kA 8/20 μ s

Nominal Discharge Current (In), UL: 20 kA 8/20 μ s

Max Discharge Current (Imax), Per Phase: 100 kA 8/20 μ s

Impulse Current (Iimp), Per Mode: 12.5 kA 10/350 μ s

Voltage Protection Rating (VPR), L-N: 1,200 V @ 3 kA;1,800 V @ 20 kA

Status Indication: LED;Mechanical flag;Audible alarm

Surge Counter: No

Technology: TD technology with thermal disconnect;Over-current replaceable cartridge fusing

Remote Contacts: Yes

Lead Size: #10

Lead Length: 30"

Ground Lead Length: 36"

Temperature: -40 to 176 °F

Enclosure Material: Metal

Enclosure Rating: IP 65;NEMA®-4

Mounting: 3/4" straight nipple

Width (W): 3.310"

Height (H): 9.450"

Depth (D): 3.070"


Unit Weight: 3.100 lb

Certification Details: UL® 1449 Edition 4 Type 1/2, 20 kA Mode

Complies With: ANSI®/IEEE® C62.41.2-2002 Cat A, Cat B, Cat C;ANSI®/IEEE® C62.41.2-2002 Scenario II, Exposure 3, 100 kA 8/20 μ s, 10 kA 10/350 μ s;IEC® 61643-1 Class I, Class II

Replacement Module: TDS150M277

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper

installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF TRACER

© 2022 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners.

nVent reserves the right to change specifications without notice.