

# REPLACEMENT MODULE FOR UTB, SINGLE PAIR ISOLATED GROUND, 0-3 VAC, 0-5 VDC UN

## CATALOG NUMBER

**UTB5SPGM**



## CERTIFICATIONS



## FEATURES

Multi-stage protection and fine over-voltage protection helps ensure lowest residual surge voltages reach sensitive equipment

Common-mode and differential-mode protection protects against both possible surge conditions

Surge rating to 20 kA 8/20  $\mu$ s is ideal for exposed wiring

## PRODUCT ATTRIBUTES

Nominal System Voltage (Un): 0 - 3 VAC;0 - 5 VDC

Max Continuous Operating Voltage (Uc): 5 VAC;7 VDC

Rated Load Current (IL): 2 A

Frequency: 0.5 MHz

Loop Resistance: 1  $\Omega$

Max Discharge Current (Imax), L+L-PE: 20 kA 8/20  $\mu$ s

Protection Modes: Common;Differential

Technology: Gas Discharge Tube (GDT);Metal Oxide Varistor (MOV);Silicon Avalanche Diode (SAD)

Voltage Protection Level (Up), L-L: 10 V @ 3 kA

Temperature: -4 to 149 °F

Enclosure Material: UL® 94V-0 Thermoplastic

Depth (D): 2.060"


Height (H): 1.700"

Width (W): 0.470"

Unit Weight: 0.050 lb

Complies With: ANSI®/IEEE® C62.41.2-2002 Cat A, Cat B, Cat C

## DIAGRAMS



## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical Support

### Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

### Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

### APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:  
nVent.com **CADDY ERICO HOFFMAN RAYCHEM SCHROFF**  
**TRACER**