


## ABS ADJUSTABLE BUSBAR SUPPORT INSULATOR MODULE, 4,500 A MAX

### CATALOG NUMBER

**ABS3-10MOD**



### CERTIFICATIONS



### FEATURES

Modules provide flexibility to select distance between phases and supports

Extremely robust construction

Halogen free insulators

RoHS compliant

### PRODUCT ATTRIBUTES

Article Number: 560900

Material: Steel;Glass Fibre Reinforced Polyamide;Stainless Steel 304 (EN 1.4301)

Finish: Electrogalvanized

Max Working Voltage, IEC (Ui): 1,000 VAC;1,500 VDC

Working Temperature: -40 to 266 °F

Complies With: IEC® 60439.1;IEC® 61439.1;IEC® 60695-2-11 (Glow Wire Test 960 °C)

Flammability Rating: UL® 94V-0

Typical Application Current Rating: 4,500 A Max

Busbars per Phase: 1 – 3

Busbar Thickness: 0.39"

Busbar Width: 1.970" – 4.920"

Width: 4.880"


Depth: 2.640"

Unit Weight: 1.790 lb

## ADDITIONAL PRODUCT DETAILS

ABS Adjustable Busbar Support High Ampacity Kit available to support up to 200 mm (7.87") busbar width for applications up to 7400 A.

## DIAGRAMS



## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical Support

### Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

### Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

### APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

**nVent.com** CADDY ERICO HOFFMAN RAYCHEM SCHROFF TRACER

© 2022 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners.

nVent reserves the right to change specifications without notice.