


CABS MODULE KIT WITH NEUTRAL, 1-2 BUSBARS PER PHASE, 1.18"-4.72" BUSBAR WIDTH, 0.39" BUSBAR THICKNESS

CATALOG NUMBER

CABS2-10TN-MOD



CERTIFICATIONS



FEATURES

Modules provide flexibility to select distance between phases and supports

Installs quickly and easily

Halogen free insulators

RoHS compliant

PRODUCT ATTRIBUTES

Article Number: 549350

Material: Steel;Glass Fibre Reinforced Polyamide

Finish: Electrogalvanized

Typical Application Current Rating: 400 – 4,500 A

Max Working Voltage, IEC (Ui): 1,000 VAC;1,500 VDC

Working Temperature: -40 to 266 °F

Complies With: IEC® 60439.1;IEC® 61439.1;IEC® 60695-2-11 (Glow Wire Test 960 °C)

Flammability Rating: UL® 94V-0

Busbars per Phase: 1 – 2

Busbar Width: 1.180" – 4.720"

Busbar Thickness: 0.39"

Depth: 1.540"

Width: 2.950"

Unit Weight: 1.060 lb

ADDITIONAL PRODUCT DETAILS

CABS modules must be installed on CABS-APP Aluminium Profile.

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF TRACER

© 2022 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners.

nVent reserves the right to change specifications without notice.