

TRC FOUR POLE DISTRIBUTION BLOCK, 400 A



FEATURES

Transparent protection cover

Bolts included for output connections

Easy accessibility for wiring

Ready to use out of the box, saving installation time and labor

RoHS compliant

SPECIFICATIONS

Product Attribute	Value
Catalog Number	TRC-400A
Item Name	563180
Material	Copper Glass Fibre Reinforced Polyamide Plexiglass
Max Working Voltage, IEC (Ui)	1,000 V
Peak Short Circuit Current (Ipk)	118 kA
Short Term Withstand Current (Icw) 1s	28 kA
Line Side Number of Connections	1
Load Side Number of Connections	10
Thread Size 1(TS1)	M6
Thread Size 2(TS2)	M10
Width(W)	10.240"
Depth(D)	1.970"
Height(H)	13.310" – 15.350"
A	11.420"
Unit Weight	5.840 lb
Flammability Rating	UL® 94V-0


Product Attribute	Value
Complies With	IEC@ 60439.1 IEC@ 61439.1 IEC@ 60695-2-11 (Glow Wire Test 960 °C)

ADDITIONAL PRODUCT DETAILS

Thread Size 2 represents input plug.

Line side and load side number of connections are per pole.

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF TRACER

© 2022 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners.

nVent reserves the right to change specifications without notice.