

D14A MECHANICAL ANCHOR WITH EXTENSION



FEATURES

Reduces congestion

Utilizes standard nVent LENTON accessories

Head area exceeds 10x bar area (net 9x)

Step machined in anchor to allow room for the installation tool on sizes 28 mm (#9) and larger

Components also sold separately

Available in customer specified lengths

SPECIFICATIONS

Finish Plain

Material Steel

Catalog Number	Rebar Size, US	Rebar Size, Canada	Diameter 2(Ø2)	Diameter 1(Ø1)	Length 1(L1)	Length 2(L2)	Bar Depth(BD)	Unit Weight
EL25D14A125N	#8	25M	3.150"	1.380"	4.920"	3.350"	1.57"	4.430 lb
EL28D14A130N	#9	30M	3.740"	1.570"	5.120"	3.460"	1.65"	5.580 lb
EL32D14A138N	#10		4.130"	1.770"	5.430"	3.660"	1.78"	6.950 lb

Designed to Meet

ACI 318;AS3600;ASTM A970

ADDITIONAL PRODUCT DETAILS

The nVent LENTON D14A Mechanical Anchor with Extension provides a method of splicing and anchoring reinforcing bar in segmental concrete construction applications that have limited space or are severely congested. The large head significantly reduces required embedment lengths. The anchors are a combination of standard nVent LENTON Terminator D14 Mechanical Anchors and EFLM Female-to-Male Extensions.


Typically used in thin wall, wall/slab and beam/column applications, the D14A Mechanical Anchor with Extension easily attaches to the form panels using standard nVent LENTON accessories. When the form is stripped, the protected threaded end of the coupler is exposed. Simply remove the protective cap or accessory and install the subsequent nVent LENTON taper threaded dowel bar. This system eliminates hooked bar congestion, protruding dowels and the need to drill holes in expensive formwork.

Anchorage calculations such as concrete breakout strength and development lengths are the responsibility of the design professional.

Bar dimensions and weights listed may vary by region. Coupler sizes not shown may be available by special order. Contact your nVent LENTON representative for more information.

Thread does not need to be flush with end of nVent LENTON Terminator. Thread may be +/- 2 threads from backside of coupler.

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF TRACER

© 2022 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners.

nVent reserves the right to change specifications without notice.