

HTV SELF-REGULATING HEATING CABLE

nVent RAYCHEM HTV self-regulating heating cable is designed for freeze protection or process temperature maintenance of pipes and vessels up to 205°C continuously, with a maximum exposure temperature of 260°C. The HTV cable has a solid construction with a high power retention (HPR) heating core and pressure extruded electrical insulation. It is then integrated with a robust metallic braid and a chemically resistant fluoropolymer outer jacket.

FEATURES

High power retention (HPR) heating core

Power retention: At least 95% after 10 years

Design life: 30 years or more depending on application

Simplified design in hazardous area: T3 and T2

Longer circuit lengths due to larger cross section conductors

Fast installation: cut-to-length, multiple overlaps allowed, meter markings, user-friendly connections kits

Safe and efficient in operation: no overheating, uniform pipe temperatures, energy saving technology

Reliable during long life: 10 year product warranty available, maintenance free

SPECIFICATIONS

Catalog Number	Item Name	Supply Voltage	Area Classification	Outer Jacket Material	Ground Path Type	Max Maintain or Continuous Exposure Temperature, Power On	Max Intermittent Exposure Temperature, Power On/Off	Max Cumulative Hours for Intermittent Exposure	Nominal Power Output @ 10°C, 230V
P000004319	3HTV2-CT	190 – 277 V	Non-Hazardous, Hazardous	High Temperature Fluoropolymer	Braid	205 °C	260 °C	2000 h	9 W/m
P000004320	5HTV2-CT	190 – 277 V	Non-Hazardous, Hazardous	High Temperature Fluoropolymer	Braid	205 °C	260 °C	2000 h	16 W/m
P000004321	8HTV2-CT	190 – 277 V	Non-Hazardous, Hazardous	High Temperature Fluoropolymer	Braid	205 °C	260 °C	2000 h	25 W/m

Catalog Number	Item Name	Supply Voltage	Area Classification	Outer Jacket Material	Ground Path Type	Max Maintain or Continuous Exposure Temperature, Power On	Max Intermittent Exposure Temperature, Power On/Off	Max Cumulative Hours for Intermittent Exposure	Nominal Power Output @ 10°C, 230V
P000004322	10HTV2-CT	190 – 277 V	Non-Hazardous, Hazardous	High Temperature Fluoropolymer	Braid	205 °C	260 °C	2000 h	32 W/m
P000004323	12HTV2-CT	190 – 277 V	Non-Hazardous, Hazardous	High Temperature Fluoropolymer	Braid	205 °C	260 °C	2000 h	38 W/m
P000004324	15HTV2-CT	190 – 277 V	Non-Hazardous, Hazardous	High Temperature Fluoropolymer	Braid	205 °C	260 °C	2000 h	48 W/m
P000004325	20HTV2-CT	190 – 277 V	Non-Hazardous, Hazardous	High Temperature Fluoropolymer	Braid	205 °C	260 °C	2000 h	64 W/m

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

Tel +1.800.545.6258
 Fax +1.800.527.5703
thermal.info@nvent.com

Europe, Middle East, Africa

Tel +32.16.213.511
 Fax +32.16.213.604
thermal.info@nvent.com

Asia Pacific

Tel +86.21.2412.1688
 Fax +86.21.5426.3167
cn.thermal.info@nvent.com

Latin America

Tel +1.713.868.4800
 Fax +1.713.868.2333
thermal.info@nvent.com



Our powerful portfolio of brands:

nVent.com **CADDY ERICO HOFFMAN RAYCHEM SCHROFF TRACER**

© 2022 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners.

nVent reserves the right to change specifications without notice.