

nVent CADDY Pyramid Rooftop Anchor System

SBS Adhered Anchor

**These instructions are for Built-up and SBS roof systems.*


Before you start:

Inspect the existing roof with a qualified professional to ensure that it is in good condition and meets local codes and manufacturer's warranty requirements. Contact nVent Customer Care for a list of qualified installation professionals.

Layout:

Appropriate frequency and spacing of the attachment points should be determined by a qualified professional for seismic requirements, compressive strength of the roofing assembly, structural load capacity, and local building code requirements. The roof surface should be clean, free of foreign debris, and dry prior to installation. Installation should be done by a qualified professional to maintain roof warranty requirements. Convey the designed layout onto the roof surface, creating crosshatches. Pair the alignment marks on each side of the CRAU26SW12C with the crosshatches previously prepared on the roof surface.

Prior to adhering the Anchor mount into place, be sure the placement is accurate.



Step 1: Once properly aligned, outline the target area and remove the target. Secure the plate with the approved fasteners from nVent, per engineering requirements. Use 8 screws, purchased separately.



Step 2: Prime the area and plate with a roofing manufacturer approved primer and allow to dry to the touch.

WARNING:

1. nVent products shall be installed and used only as indicated in nVent product instruction sheets and training materials. Instruction sheets are available at www.nVent.com and from your nVent customer service representative.
2. nVent products must never be used for a purpose other than the purpose for which they were designed or in a manner that exceeds specified load ratings.
3. All instructions must be completely followed to ensure proper and safe installation and performance.
4. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and/or death, and void your warranty.
5. Products that are manufactured using spring steel components shall be used only in a non-corrosive indoor environment.
6. All pipe supports, hangers, intermediate components and structural attachments must **ONLY** be used as described herein and are **NEVER** to be used for any other purpose.

NOTE: All load ratings are for static conditions and do not account for dynamic loading such as wind, water or seismic loads, unless otherwise noted.

The customer is responsible for:

- a. Conformance to all governing codes.
- b. The integrity of structures to which the products are attached, including their capability of safely accepting the loads imposed, as evaluated by a qualified engineer.
- c. Using appropriate industry standard hardware as noted above.

SAFETY INSTRUCTIONS:

All governing codes and regulations and those required by the job site must be observed. Always use appropriate safety equipment such as eye protection, hard hat, and gloves as appropriate to the application.


nVent, nVent CADDY, nVent ERICO Cadweld, nVent ERICO Critec, nVent ERICO, nVent ERIFLEX, and nVent LENTON are owned by nVent or its global affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without prior notice.

TECHNICAL SUPPORT:
www.nVent.com


CFS588_B

1 OF 2

© 2018 nVent All Rights Reserved



Step 3: Apply adhesive to the substrate with a trowel. (Check mfg.'s recommendations for thickness of adhesive.) Install the die cut asphalt target into the adhesive, pressing downward on the target to fully embed it in the adhesive. Allow a 1/4" bleed to occur on all edges.



Step 4: Apply loose granules over exposed adhesive. Install the 2" separator around the bolt. This can be adhered in place, but is not required.

Step 5: Install ancillary components using a stainless steel 3/8"-16 nut and lock washer. The recommended torque for the CRAU26SW12C is 20\25 ft lbs.